



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SJEW123BK250 12/3 Sjew 300V Black Cord-250' Reel

Coleman Cable

Catalog Number	SJEW123BK250
Manufacturer	Coleman Cable
Description	Portable Cord, Stranded, 65/30 MM Core Strands, #12 Awg Conductor Size, Copper Conductor Material, Thermoplastic Jacket Material, Thermoplastic Insulation Material, 300 V, Black, Green and White, 3 Conductors, 250 FT Overall Length, 0.435 In Outside Diameter, 0.031 In Insulation Thickness, +90 °C (UI) Operating Temperature, 0.13 LB/MFT
Weight per unit	0.1300 (lbs/ft)
Product Category	SJ-Sje

Features

Stranding	65/30 STRANDS
-----------	---------------

Material, Color, and Finish

Color Code	BLACK, GREEN, WHITE
Jacket Color	BLACK

Dimensions and Weight

Length	250 FT
Outer Diameter	0.435 INCH

Descriptions

Additional Information	ROHS Compatible; Applicable Standard NEC 400, Federal Specification JC-580B; Current Rating 25 Ampere; Insulation Thickness 0.031 Inch
Commodity Description	Sj-Sje-300v Cord & Cable
Description	12/3 SJEW 300V BLACK CORD-250' REEL

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892238087
Model	233
UPC	029892238087

Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable
Type	SJEW

Packaging

Carton	250
Weight Per foot	0.13



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	INDUSTRIAL CONTROL AND ROBOTIC SYSTEM/MINING/MOTOR CONTROL/OUTDOOR/PUSHBUTTON REMOTE CONTROL/STAGE EQUIPMENT AND LIGHTING
Approval	UL, CSA, MSHA
Temperature Rating	90 DEG C (UL), 60 DEG C (CSA)