



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5361USBBK Disc Sub Tr5362usbbk *Pass & Seymour/Legrand*

Catalog Number	TR5361USBBK
Manufacturer	Pass & Seymour/Legrand
Description	Decorator Combination 20A 125V Tamper-Resistant Outlet With Two Usb Chargers - Black
Weight per unit	0.3170 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
Material	Thermoplastic
Number of Wires	3
Phase	Single
Poles	2
Voltage Rating	125
Wire Size	14 -10

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Depth	1.31
Height	4.18
Size	1.31" (D) x 1.60" (W) x 4.18" (H)
Width	1.60

Descriptions

Description	DISC SUB TR5362USBBK
extra long description	P&S TR5361USBBK 20A TR SPEC GRD W/2
Long Description	Decorator Combination 20A 125V Tamper-Resistant Outlet with Two USB Chargers - Black
Product Type	20A TR Spec GRD W/2.1A Usb CHRG BK
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger receptacle features 2.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007029109
Manufacturers Part Number	TR5361USBBK
sub brand	Pass & Seymour
UPC	785007029109

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Tamper-Resistant USB Single Receptacle

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	50
Weight Per each	0.317

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-20R
standard	CSA Listed, ETL Lsted, FSUL, UL Listed, RoHS
Temperature Rating	Maximum continuous +60°C, minimum -40° without impact