

14U SmartRack Extra Deep Small Server Rack Enclosure, Doors & Side Panels Included

MODEL NUMBER: SR14UBDP



14U rack cabinet houses, organizes and secures deeper standard-width rack equipment in high-density server and IT networking areas.

Features

Deep Server Cabinet Accommodates 14U of Standard Rack Equipment This SmartRack® 14U rack enclosure is designed for network wiring closets, retail locations, classrooms, back offices and other areas with essential rack-mount IT equipment. It supports mounting of equipment up to 42 inches deep. This allows high-density equipment installations, extra space for cable management, and room for removing hot-swap power supplies from the rear of mounted devices. Constructed from heavy-duty steel with a durable black powder-coated finish, the SR14UBDP has a maximum load capacity of 1000 lbs (453.6 kgs).

Keeps Important Equipment Secure and Well Ventilated The reversible front and rear doors and removable side panels lock securely to help prevent damage, tampering or theft. The doors, side panels and top panel are designed for quick release, making it easy to access connected equipment and cabling with little effort. Convenient top access ports and an open bottom allow easy cable routing through the cabinet. The vented doors draw in cool air from outside and remove warm air to keep your equipment cool and functioning at their peak. The top panel also supports the installation of optional case fans (such as Tripp Lite's SRFANWM).

Easy Enclosure Deployment and Equipment Installation This 14U server rack comes fully assembled for quick and easy deployment. Four metal casters (and installation hardware) are included that let you maneuver the rack cabinet over a level, smooth, stable surface and through a standard doorway into position, where it can be stabilized by adjusting the levelers. Front and rear mounting rails adjust in quarter-inch increments to accommodate equipment up to 42 inches deep. Adjustable vertical cable management rails help keep the back of the rack organized.

Meets Payment Card Industry Standards The SR14UBDP provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

Specifications

Highlights

- 14U rack constructed from powder-coated steel that stands up to tough environments
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Ships fully assembled for quick deployment on included metal casters
- Provides physical equipment and media security required for PCI DSS compliance
- Front and rear mounting rails accept standard rack equipment up to 42 in. deep

Applications

- Store and organize deeper-than-usual rack-mount equipment in a network closet, data center or other area where you need components to be secure

Package Includes

- SR14UBDP 14U Server Rack
- (60) M6 screws
- (60) M6 washers
- (60) M6 cage nuts
- (2) Keys
- SRCASTER rolling caster kit
- Owner's manual



OVERVIEW	
UPC Code	037332197917
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Factory Preset Rack Depth (in.)	28.31
Factory Preset Rack Depth (cm)	71.9
Factory Preset Rack Depth (mm)	719
Maximum Device Depth (cm)	93.98
Maximum Device Depth (in.)	37
Maximum Device Depth (mm)	940
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Rack Height	14U
Shipping Dimensions (hwd / cm)	85.22 x 65.71 x 116.79
Shipping Dimensions (hwd / in.)	33.55 x 25.87 x 45.98
Shipping Weight (kg)	70.76
Shipping Weight (lbs.)	156.00
Unit Dimensions (hwd / cm)	71.70 x 60 x 110.80
Unit Dimensions (hwd / in.)	28.230 x 23.63 x 43.620
Unit Weight (kg)	47.63
Unit Weight (lbs.)	105
Weight Capacity - Rolling (kg)	454
Weight Capacity - Rolling (lbs.)	1000
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
Rack Depth	Standard
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Grounding Lug	Front and back door frames



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Certifications	RoHS; UL/CSA 60950-1; IP20 Protection Rating
Approvals	EIA/ECA-310-E
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>