

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive 79936-0000, TX El Paso Phone: 915-995-8443 Fax: 915-245-2106

TY528M 14.19" "Ty-Rap" Cable Tie Abb Installation Products, Inc

Catalog Number	TY528M
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, UI/En/CSA62275 Type 2/21S Rated For Ah-2 Plenum or As A Flexible Cable and Conduit Support, Length Of 360.5MM (14.2 Inches), Width Of 4.82MM (0.19 Inches), Thickness Of 1.4MM (0.05 Inches), Tensile Strength Rating Of 222 Newtons (50 Pounds)
Weight per unit	0.0070 (lbs/each)
Product Category	Cable Ties & Wraps
Features	,
Tensile Strength	50
Dimensions and Weight	
Length	14.2
Thickness	0.05
Width	0.19
Descriptions	
Description	14.19" "TY-RAP" CABLE TIE
extra long description	ABB TY528M CBL TIE 50LB 14 NAT NYLO
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum or as a Flexible Cable and Conduit Support, Length of 360.5mm (14.2 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.4mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)
Product Type	CBL Tie 50LB 14 Nat Nylon 2-PC D
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time
Manufacturer Information	
Brand	Ty-Rap
GTIN	00786210805139
Manufacturers Part Number	TY528M
UPC	786210805139



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive 79936-0000, TX El Paso Phone: 915-995-8443 Fax: 915-245-2106

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Туре	HIGH PERFORMANCE
Packaging	
Carton	100
Package	500
Weight Per each	0.007

UL E49405 / UL E49405