



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



U7021DLTG 200A 4T Meter Socket W/Hub

Milbank MFG.

Catalog Number	U7021DLTG
Manufacturer	Milbank MFG.
Description	Meter Socket, 200 A, 15-1/2 In Overall Height, 8 In Overall Width, 4-1/8 In Overall Length, Surface Mount, 1 Phase, 2 In Bolt-On Hub, 4 Jaws, 600 V Ac, #6 Awg to 350 Kcmil Wire Size, Overhead Feed, 10.5 LB
Weight per unit	10.5 (lbs/each)
Product Category	Residential Single Meter Socke

Features

Bypass Switch Type	NO
Circuit Configuration	1-Phase
Knockouts	(1) 1/4 INCH, (1) (1/4-INCH-1/2 INCH) CONCENTRIC KNOCKOUT, (3) 2 1/2 INCH
Neutral Type	TRIPLEX GROUND
Service Type	OVERHEAD

Material, Color, and Finish

Enclosure Material	Powder Coated G90 Galvanized Steel
--------------------	------------------------------------

Dimensions and Weight

Size	8 INCH W X 4-1/8 INCH D X 15-1/2 INCH H
------	---

Descriptions

Commodity Description	RESIDENTIAL SINGLE METER SOCKETS
Description	200A 4T METER SOCKET W/HUB

Manufacturer Information

GTIN	00784572139763
Model	U7021
UPC	784572139763

Taxonomies, Classifications, and Categories

Category Description	TEMP. POWER PANELS & ACCESSORIES
Type	RINGLESS

Packaging

Carton	1
Package	10
Weight Per each	10.5

Uses, Certifications, and Standards


Approval	UL mA
Enclosure	NEMA 3R
Mounting	SURFACE

6

200 AMP
SINGLE
POSITION
SOCKETS


Single Position Sockets

200 Amps | 4 & 5 Terminals | Ringless | 600 VAC



7021

U7021-RL-TG



7040

U7040-RL-TG

200 Amps | 4 & 5 Terminals | Single Position | Ringless

Catalog Number	Terminals	Hub	Connectors CU/AL		Dimensions			Knockouts		
			Line	Load	D"	W"	H"	1	2	3
U7021-RL-TG	4	H.O.	#6-350	#6-350	4 $\frac{1}{8}$	8	15 $\frac{1}{2}$	2 $\frac{1}{2}$	1 $\frac{1}{4}$, $\frac{1}{2}$	1 $\frac{1}{4}$
U7021-DL-TG	4	2"	#6-350	#6-350	4 $\frac{1}{8}$	8	15 $\frac{1}{2}$	2 $\frac{1}{2}$	1 $\frac{1}{4}$, $\frac{1}{2}$	1 $\frac{1}{4}$
U7040-RL-TG	4	H.O.	#6-350	#6-350	4 $\frac{1}{8}$	11	14 $\frac{5}{8}$	2 $\frac{1}{2}$	1 $\frac{1}{4}$, $\frac{1}{2}$	1 $\frac{1}{4}$
U7021-RL-TG-5T	5	H.O.	#6-350	#6-350	4 $\frac{1}{8}$	8	15 $\frac{1}{2}$	2 $\frac{1}{2}$	1 $\frac{1}{4}$, $\frac{1}{2}$	1 $\frac{1}{4}$

Notes

- **Other Options:** These units are also available in aluminum and horn bypass. Consult factory for more details.
- **Fifth Terminal:** For field mounted fifth terminal, order catalog number **K5T** to fit into square opening at the 9 o'clock position. For factory-installed fifth terminal, add suffix **-5T** to catalog number.
- **Triplex Ground (-TG):** Factory installed.
- **Connectors:** Extruded aluminum connectors are tin plated.



Utility requirements for this equipment may vary. Always consult the serving utility for their requirements before ordering or installing equipment.