

## LIQUID-TUFF™

### UL Liquidtight Flexible Steel Conduit, Type LFMC (Gray, Black, Red, Orange, Yellow, Green)

#### Scope

This specification covers AFC Cable Systems, Inc. UL LIQUID-TUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code. The product is Underwriters Laboratories Inc. (UL) Listed for 80°C (176°F) in a dry location, 60°C (140°F) in a wet location and 70°C (158°F) in an oily location. It is also UL Listed in all trade sizes for direct burial in either earth or concrete encasement, outdoor use and sunlight resistance. This LIQUID-TUFF® is now UL Listed for 70°C OIL RESISTANT applications. In addition the product is CSA certified for use at 75°C (167°F) in dry and oily locations and for minus -30°C (22°F) low temperature applications. This Liquidtight Flexible Steel Conduit is manufactured and tested in accordance with Underwriters Laboratories Inc. Standard UL 360 and CSA International Standard CSA C22.2 Number 56. The product carries the UL Listing Mark and the CSA Certification Mark.

#### Construction

The Type UL Liquidtight Flexible Steel Conduit shall be formed from a zinc coated galvanized low carbon steel strip having a uniform width and thickness. The construction shall be in accordance with UL 360 and CSA C22.2 Number 56 requirements. The finished Type LFMC dimensions shall be in accordance with Table 5.1 of UL 360 and Table 2 of CSA C22.2 No. 56 which are summarized in Table 3.

#### Grounding

Permanent circuit ground protection is provided through the continuous bonding strip built into the conduit core in sizes 3/8" through 1-1/4". A separate grounding conductor is required by the NEC® for trade sizes 1-1/2" and larger. The Canadian Electric Code requires a grounding conductor for all trade sizes of Type UL Liquidtight Flexible Steel Conduit.

#### Jacket - PVC

A rugged moisture, oil and sunlight resistant polyvinyl chloride (PVC) jacket shall be applied directly over the flexible metal conduit with a wall thickness in accordance with Table 4.1 of UL 360 and Table 4 of CSA C22.2 No.56 which are summarized in Table 2. Jacket Color: Gray, Black, Red, Orange, Yellow, or Green

#### Markings

The surface of the outer jacket shall be clearly marked with a legible print legend in compliance with UL 360, and CSA C22.2 No. 56.

#### Performance Tests

In accordance with UL 360 and CSA C22.2 No. 56, the completed UL LIQUID-TUFF™ Liquidtight Flexible Steel Conduit shall meet all of the performance requirements outlined in Appendix A.



#### Description

- UL bonding strip 3/8" – 1-1/4" for grounding
- UL Liquidtight all sizes
- Sunlight resistant
- Flame retardant PVC jacket
- Hot dipped zinc galvanized low carbon steel core
- Available in Gray, Black, Red, Orange, Yellow or Green

#### Temperature Rating

- 80°C/176°F
- 60°C/140°F Wet
- 70°C/158°F Oil
- -30C/-22F Low temperature

#### Applications

- NEC® 350 Liquidtight Flexible Metal Conduit Type LFMC
- Suitable for Wet Locations
- Suitable for Direct Burial in earth
- Suitable for Concrete Embedment
- Suitable for exposure to Sunlight and Weather
- Suitable for grounding in 3/8 to 1 ¼ trade sizes per NEC® 250.118(6)
- Suitable for Flexible Connections in Hazardous Locations: Class I Div 2 NEC® 501.10(B)(2)(4), Class II Div 1 NEC® 502.10(A)(2)(2), Class II Div 2 NEC® 502.10(B)(2), Class III Div 1 NEC® 503.10(A)(3)(2) and Class III Div 2 NEC® 503.10(B).
- Suitable for Raised Computer Room Floors per NEC® 645.5(E)(2)
- Suitable for Service Entrance Wiring up to 6 feet per NEC® 230.43(15)
- Suitable for Marinas and Boatyards per NEC® 555.13(A)(1)
- Suitable for Electric signs and Outdoor Lighting per NEC® 600.31(A)(1) and 600.32(A)(1)
- Suitable for Flexible Connections for hoists and cranes per NEC® 610.11(C)
- Suitable for wiring Elevators, Dumbwaiters, Escalators, Moving Walks, Platforms and Stairway Chairlifts per NEC® 620.21
- Suitable for Motors for Permanently Installed Pools where Flexible Connections are required per NEC® 680.21(A)(3)
- Suitable for Spas and Hot Tubs where Flexible Connections are required per NEC® 680.42(A)(1)
- Suitable for feeders for Natural and Artificially Made Bodies of Water where Flexible Connections are required per NEC® 682.13
- Suitable for Solar Photovoltaic (PV) Systems per NEC® 690.31(A)
- Suitable for Fire Pump Wiring per NEC® 695.6(D)
- Suitable for Electric Fire Pump Control Wiring per NEC® 695.14(E)

#### References & Ratings

- Underwriters Laboratories Inc. Standard: UL 360 File: E26540
- CSA Group: Standard: C22.2 No. 56 File: 51593
- NFPA 70 NEC® Article 350
- Canadian Electric Code (CEC) Part I Clause 12-1300
- UL Listed in all Trade Sizes for Direct Burial which includes Concrete Encasement
- Conduit in Trade Sizes 1 ½ and larger require an equipment grounding conductor per NEC® 350.60

ORDERING INFORMATION						PRODUCT DIMENSIONS/BEND RADIUS			
Product Code	Trade Size (inches)	Trade Size (mm)	Coil Length (feet)	Reel Length (feet)	Approx. Weight 100 feet (pounds)	External Diameter (inches)		Internal Diameter (min/max) inches	Bend Radius (inches)
						Over Jacket (min/max)			
<b>GRAY*</b>									
6201-30-00	3/8	12	100'	—	24	0.690/0.710		0.484/0.504	2
6201-45-00	3/8	12	—	500'	24	0.690/0.710		0.484/0.504	2
6201-60-00	3/8	12	—	1000'	24	0.690/0.710		0.484/0.504	2
6201-65-00	3/8	12	—	2500'	24	0.690/0.710		0.484/0.504	2
6202-30-00	1/2	16	100'	—	31	0.820/0.840		0.622/0.642	3.25
6202-45-00	1/2	16	—	500'	31	0.820/0.840		0.622/0.642	3.25
6202-60-00	1/2	16	—	1000'	31	0.820/0.840		0.622/0.642	3.25
6202-68-00	1/2	16	—	3500'	31	0.820/0.840		0.622/0.642	3.25
6203-30-00	3/4	21	100'	—	49	1.030/1.050		0.820/0.840	4.25
6203-45-00	3/4	21	—	500'	49	1.030/1.050		0.820/0.840	4.25
6203-60-00	3/4	21	—	1000'	49	1.030/1.050		0.820/0.840	4.25
6203-66-00	3/4	21	—	2000'	49	1.030/1.050		0.820/0.840	4.25
6204-30-00	1	27	100'	—	79	1.290/1.315		1.041/1.066	6.5
6204-41-00	1	27	—	400'	79	1.290/1.315		1.041/1.066	6.5
6204-64-00	1	27	—	1250'	79	1.290/1.315		1.041/1.066	6.5
6205-24-00	1-1/4	35	50'	—	103	1.630/1.660		1.380/1.410	8
6205-40-00	1-1/4	35	—	200'	103	1.630/1.660		1.380/1.410	8
6205-47-00	1-1/4	35	—	750'	103	1.630/1.660		1.380/1.410	8
6206-24-00	1-1/2	41	50'	—	109	1.865/1.900		1.575/1.600	9
6206-35-00	1-1/2	41	—	150'	109	1.865/1.900		1.575/1.600	9
6206-62-00	1-1/2	41	—	600'	109	1.865/1.900		1.575/1.600	9
6207-24-00	2	53	50'	—	146	2.340/2.375		2.020/2.045	11.12
6207-30-00	2	53	—	100'	146	2.340/2.375		2.020/2.045	11.12
6207-80-00	2	53	—	300'	146	2.340/2.375		2.020/2.045	11.12
6208-22-00	2-1/2	63	25'	—	169	2.840/2.875		2.480/2.505	14.62
6208-79-00	2-1/2	63	—	275'	169	2.840/2.875		2.480/2.505	14.62
6209-22-00	3	78	25'	—	195	3.460/3.500		3.070/3.100	17.5
6209-56-00	3	78	—	175'	195	3.460/3.500		3.070/3.100	17.5
6220-22-00	3-1/2	91	25'	—	230	3.960/4.000		3.500/3.540	20
6220-56-00	3-1/2	91	—	175'	230	3.960/4.000		3.500/3.540	20
6210-22-00	4	103	25'	—	250	4.460/4.500		4.000/4.040	24
6210-30-00	4	103	—	100'	250	4.460/4.500		4.000/4.040	24

NOTE: All dimensions and weights are subject to normal manufacturing tolerances. Review NEC® 350.60 and 250.118(6) for grounding requirements. Made in USA of US and/or imported materials.

(Chart continues on next page.)