

T120L9K2



Article Number: 111-12419

Heavy Duty Cable Tie, 30" Long, 120lb Tensile Strength, PA66, Natural, 50/pkg



Base Data

Local Order Number T120L9K2

Type T120L

Color Natural (NA)

- Features and Benefits**
- Heavy duty design to offer higher tensile strength.
 - Head design provides high tensile strength with very low insertion force.
 - Bent tail ensures a quick and simple installation.

Product Description HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Fixation Method (FF) None

Identification Plate Position none

Releasable Closure (Yes/No) No

Tie Closure plastic pawl

Variant Inside Serrated

Short Description Heavy Duty Cable Tie, 30" Long, 120lb Tensile Strength, PA66, Natural, 50/pkg

Product Dimensions

Minimum Tensile Strength (imperial) 120.0 lbs

Minimum Tensile Strength (N) 535.0 N

Length L (imperial) 30.0 "

Length L (metric) 760.0 mm

Width W (imperial) 0.3 "

Width W (metric) 7.6 mm

Bundle Diameter min (imperial) 0.23 "

Bundle Diameter min (metric) 5.76 mm

Bundle Diameter max (imperial) 8.85 "

Bundle Diameter max (metric) 225.0 mm

Thickness T (imperial) 0.075 "

Cable Tie Head Height (Metric) 7.8 mm

Cable Tie Head Length (metric) 10 mm

Cable Tie Head Width (metric) 13 mm

Cable Tie Head Length (imperial) 0.393 "

Cable Tie Head Width (imperial) 0.502 "

Thickness T (Metric) 1.9 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	50
Carton Quantity	1000
Weight (Metric)	11.5 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
US MILSPEC	MS3367-6-9
CSA Certified	No
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	Yes
Certification / Specification	MIL 53421 UL ZODZ2.E64139
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes