

S and T Series

Specifications Description: Dual-element, time-delay plug fuse.

Dimensions:

- S Rejection base
- T Edison base

Construction:

- S Plastic base with rejection threads
- T Brass threads with plastic body

Ratings:

- Volts 125Vac
- Amps S Series: ¼-30A
 - T Series: ³/₀-30A
 - IR 10kA RMS Sym.

Agency Information: CE, Std. 248-11, Type S and T: UL Listed (0-6¼) Guide JFHR, File E56412 (7-30A) Guide JEFV, File E12112; CSA Certified, Class 1423-01, File 53787.

Features and Benefits

- Time-delay, dual-element T Series Edison base plug fuses provide small motor overload protection when used with box cover units.
- Time-delay, dual-element S Series plug fuses provide a rejection feature (when used alone or with Fustat adapters to retrofit Edison base holders) to prevent overfusing of branch circuits.

Typical Applications

- S Series Residential Load Centers
- T Series Box Cover Units for small motor overload protection
- · Applications benefiting from fuse rejection (S Series only)

S Series Catalog Numbers (Amps)

S-1/4	S-1/10	S-1-‰	S-2-½	S-4	S-7	S-14
S-¾	S-1	S-1-1%	S-2-1/10	S-4-1/2	S-8	S-15
S-1/10	S-1-1⁄8	S-2	S-3	S-5	S-9	S-20
S-½	S-1-¼	S-2-1⁄4	S-3-1/10	S-6	S-10	S-25
S-%	S-1-1/10	S-5-%	S-3-½	S-6-1/4	S-12	S-30

T Series Catalog Numbers (Amps)

		5	· · ·	,		
T-¾	T-1-1⁄8	T-2-1⁄4	T-4	T-7	T-15	
T-1/10	T-1-¼	T-2-½	T-4-½	T-8	T-20	
T-½	T-1-1/10	T-2-%	T-5	T-9	T-25	
T-%	T-1-%	T-3	T-5-%	T-10	T-30	
T-1/10	T-1-%	T-3-1/10	T-6	T-12	EDA*	
T-1	T-2	T-3-½	T-6-1⁄4	T-14	EDN**	

* Non-conductive Edison base dummy. Not a fuse.

** Conductive Edison base dummy. Not a fuse

Data Sheet: 1032 (S) & 1034 (T)

Recommended Fuse Holders For S & T Series Plug Fuses

- See page 14
- · See page 42 for Fustat adapters for use with S Series

P & TC Series

Specifications Description: P Series - Type P Dual-element fuse TC Series - Type D Dual-element,

Time-delay fuse

Dimensions: Edison base

Construction: Brass threads with plastic body

Ratings:

Volts — 125Vac or less

Amps - 15-30A

IR — 10kA

Agency Information:

P Series - CSA Certified

TC Series - CSA Certified (Class 1423-01, File # 53787)

Features and Benefits

P Series

- "P" rating for Canadian applications.
- Non-time delay for non-inductive loads
- TC Series
 - "D" rating for Canadian applications
 - · Heavy duty TC fuses are industrial strength products, featuring dual-element construction.
 - This spring loaded design provides superior short-circuit and overload protection.
 - The TC fuses have more time-delay than the medium duty fuses in order to better protect industrial motors and residential circuits.

Typical Applications

- P Series Non-inductive loads, residential load centers
- TC Series Box Cover Units for small motor overload protection

P Series Catalog Numbers (Amps)

P-15	P-20	P-25	P-30
------	------	------	------

TC Series Catalog Numbers (Amps) TC-20 TC-15 TC-25 TC-30

Data Sheet: 1039 (TC Series only)

- Recommended Fuse Holders For P & TC Series Plug Fuses
- See page 14
- · See page 42 for Fustat adapters for use with S Series







