



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## UF102WG250 10/2WG Uf Cable-250'

*Southwire Company*

Catalog Number	UF102WG250
Manufacturer	Southwire Company
Description	Underground Feeder Cable, Solid, 1 Strand, #10 Awg Conductor Size, Copper Conductor Material, PVC Jacket Material, PVC Insulation Material, 600 V, 30 A, Gray, 2 Conductors, 250 FT Overall Length, 518 X 215 Mil Outside Diameter, 24 Mil Insulation Thickness, +90 °C Operating Temperature, 140 LB/MFT
Weight per unit	0.1406 (lbs/ft)
Product Category	Uf-NMcb-Ug-Nmwu

### Features

Ground Conductor Size	10 AWG
Ground Type	WITH GROUND WIRE
similar brands	Romex®
Stranding	SOLID

### Dimensions and Weight

Length	250 FT
Length in ft	250 VAC
Outer Diameter	518 MIL X 215 MIL

### Descriptions

Also Known As...	Non-Metallic Sheathed Cable Thermoplastic-Sheathed Cable 220 Wire
Commodity Description	COPPER NON-METALLIC CABLE-UF-NMcb-UG-NMWU
Description	10/2WG UF CABLE-250'

### Manufacturer Information

Brand	Copper
GTIN	00032886166105
UPC	032886166105

### Taxonomies, Classifications, and Categories

Category Description	ROMEX (RX)& UF CABLE
Type	UF-B

### Availability

minimum qty	250
-------------	-----

### Packaging

Carton	250
Weight Per foot	0.1406



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Approval ..... UL 83/493

Temperature Rating ..... 90 DEG C

# Copper UF-B



**Underground Feeder and Branch Circuit Cable. 600 Volt. Copper Conductors. Sunlight, Moisture, and Fungus Resistant Overall PVC Jacket.**

## APPLICATIONS

Southwire® copper UF-B cable is generally used as feeder to outside post lamps, pumps, and other loads or apparatus fed from a distribution point in an existing building as specified in the 2011 National Electrical Code. UF-B cable may be used underground, including direct burial. Multiple conductor UF-B cable may be used for interior branch circuit wiring in residential or agricultural buildings at conductor temperatures not to exceed 90°C (with ampacity limited to that for 60°C conductors) as specified by the National Electrical Code. UF-B can be used in applications permitted for NMC in Section 334.10(B) of the National Electrical Code. Voltage rating for UF-B cable is 600 volts.

## STANDARDS & REFERENCES

Southwire® copper UF-B cable complies with the following:

- ASTM - B3 and B-8
- UL Standard 83
- UL Standard 493
- Federal Specification A-A-59544
- National Electrical Code, NFPA 70, 2011 Edition
- RoHS/ REACH

## CONSTRUCTION

Southwire® copper UF-B cable is manufactured as a 2 or 3 conductor cable, with or without a ground wire. Copper conductors are annealed (soft) copper, solid or compressed stranded. Phase conductors are polyvinyl chloride (PVC) insulated, nylon jacketed, color coded for identification purposes. Jacketed with sunlight, moisture and fungus resistant gray PVC.



Conductor			Jacket Thickness (mils)	Ground Wire		Cable Dimension (mils)	Approx. Net Wt. Per 1000' (lbs.)	Allowable Ampacity	Standard Package
Size (AWG or kcmil)	No. of strands	Insulation and jacket thickness (mils)		Size (AWG)	No. of strands				
<b>TWO CONDUCTOR</b>									
14	1	19	30	14	1	423X168	70	15	AC
12	1	19	30	12	1	463X183	95	20	ACDE
12	1	19	30	Without Ground		386X183	70	20	AC
10	1	24	30	10	1	518X215	138	30	ACDE
8	7	35	45	10	1	678X302	222	40	BCE
6	7	35	45	10	1	770X338	303	55	BCE
<b>THREE CONDUCTOR</b>									
14	1	19	30	14	1	581X168	95	15	AC
12	1	19	30	12	1	626X183	129	20	ACD
12	1	19	30	Without Ground		581X183	107	20	A
10	1	24	30	10	1	727X215	191	30	ABC
8	7	35	45	10	1	1059X319	344	40	BCE
6	7	35	45	10	1	1223X361	478	55	BCE
+ Ampacities per National Electrical Code section 310.15 and 340.80, 2011 Edition								Package Code: A-250' B-500' C-1,000' D-2,500' E-125'	

**RECOMMENDED SAMPLE SPECIFICATIONS:**

Cable shall be UL-listed Type UF-B, suitable for operation at 600 volts or less in all installations as specified in the National Electrical Code. Conductors shall be annealed copper as manufactured by Southwire Company or approved equal.

Conductor		
Size (AWG or kcmil)	No. of strands	Stock Numbers
<b>TWO CONDUCTOR</b>		
14	1	<b>Stock #: 130542</b>
12	1	<b>Stock #: 130559</b>
12	1	<b>Stock #: 130492</b>
10	1	<b>Stock #: 130567</b>
8	7	<b>Stock #: 208587</b>
6	7	<b>Stock #: 214692</b>
<b>THREE CONDUCTOR</b>		
14	1	<b>Stock #: 130575</b>
12	1	<b>Stock #: 130583</b>
12	1	<b>Stock #: 130526</b>
10	1	<b>Stock #: 130591</b>
8	7	<b>Stock #: 147835</b>
6	7	<b>Stock #: 147827</b>