



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNF205SA 3/4" Alum Female Union

Crouse-Hinds

Catalog Number	UNF205SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Unf Union, Rigid/Imc, Female, Copper-Free Aluminum, Group B Rated, 3/4"
Weight per unit	0.1900 (lbs/each)
Product Category	Aluminum

Features

connection	Threaded
dimensions	1.9100 IN X 1.7800 IN X 1.7800 IN

Descriptions

Description	3/4" ALUM FEMALE UNION
extra long description	CRS-H UNF205 SA 3/4 NPT FEMALE AL U
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNF union, Rigid/IMC, Female, Copper-free aluminum, Group B rated, 3/4"
Product Type	3/4 NPT Female Al Unf Union
Special Features	1-13/16 In Diameter X 1-3/4 In Length

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274101835
Manufacturers Part Number	UNF205 SA
UPC	782274101835

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Package	10
Weight Per each	0.19



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2
	Group F G, Class III
standard	UL 886, CSA C22.2