

Project:	Type:	Prepared By:	Date:
-----------------	--------------	---------------------	--------------



Features and Benefits

- Replacement for conventional fluorescent T8 and T12 linear tubes
- Integral Driver enables lamp to be wired directly to line voltage without need for an external driver or ballast
- Double ended wiring method
- Works with shunted sockets.
- Approximately 50% more energy efficient when compared to Fluorescent T8 lamps
- 50,000 hour Lifespan.
- Rated for use in enclosed and open fixtures in dry or damp locations
- Diffused frosted lens will maintain the same light quality over time
- Instant on full brightness
- Environmentally friendly, no mercury used
- NSF Listed: NSF/ANSI Standard 2 - Food Equipment - Splash Zone (Not for Direct Food Zone without additional fixture considerations)
- Internal thermal fuse for added safety
- Emergency back up available. Catalog Numbers: DRI-5-EMGR-T8, DRI-10-EMGR-TYPE B
- Phase cut dimming

Technical Specifications

Performance	L70 Lifespan:	For Use Outdoors in Open Fixtures:
Product Type:	50,000 Hours	No
Linear	Construction	Beam Angle:
Input Wattage:	Material:	210°
14W	Glass	Other
Typical Lumen Output:	Bulb Shape:	Equivalency:
1800	T8	32W Fluorescent
Efficacy:	Nominal Length:	Warranty (Years):
129 lm/W	4FT	RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty .
Color Temperature:	Finish:	Electrical
5000K Daylight	Frosted	Power Factor:
CRI:	Base Type:	0.9
82	G13	

Technical Specifications (continued)

Electrical

Operating Temperature:

-20°C - 45°C

Input Voltage:

120-277V AC

Operating Frequency:

50/60 Hz

Installation

Installation Type:

Type B, Double Ended wiring

Electrical Characteristics

Input Current @ 120V:

102mA

THDi:

<20%

Compliance

UL Recognized:

Yes

UL Classified:

Yes

NSF Listed:

Meets NSF/ANSI standards for use in Food Zone (non-contact), Splash, and Non-Food Zones. Tube guard required in open fixtures.

DLC Model Number:

T8-14-48G-850-DE-BYP

CEC Status:

Lawful for sale in California

Application:

Suitable for damp locations and totally enclosed fixtures.

DLC Listed:

This product is on the Design Lights Consortium (DLC) Qualified Products List and is eligible for rebates from DLC Member Utilities. Designed to meet DLC 5.1 requirements.

DLC Product Code: PJ5VSR8I



Minimum Compartment Size

Length x Width x Height [in]	Lamp Quantity
47.8 x 23.8 x 3.0	4

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	25	48.8	5.9	5.9
PALLET	1200	49.2	39.4	46.1

Wiring Diagram



Dimension

