



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



V48M28T1516 15KVA Ventd XFMR DOE2016 Eff 3PH 480-208Y/120 150C *Eaton Corp*

Catalog Number	V48M28T1516
Manufacturer	Eaton Corp
Description	Doe 2016 Efficient Transformer, Three-Phase, PV: 480V, Taps: 2 At +2.5% Fcan, 4 At -2.5% FCBN, SV: 208Y/120V, 150°C, 15 Kva, Al Windings
Weight per unit	258.0 (lbs/each)
Product Category	Three Phase Energy Efficient D

Features

dimensions	17.7500 IN X 21.8800 IN X 28.0000 IN
Efficiency	10 CFR Part 431-2016 (DOE 2016)
Insulation Class	220 °C
kva rating	15 kVA
Number of Phases	Three-phase
Primary Voltage	480 V
Secondary Voltage	208y/120 V
Tap Size	2 at +2.5% FCAN; 4 at -2.5% FCBN

Descriptions

Description	15KVA VENTD XFMR DOE2016 EFF 3PH 480-208Y/120 150C
extra long description	ETN V48M28T1516 15KVA DOE2016 EFF 3
Features	Eaton types DS-3 (single-phase) and DT-3 (three-phase) general purpose ventilated dry-type transformers are two-winding, self-cooled, and available in a wide variety of primary and secondary voltage combinations. General purpose transformers are designed for continuous operation at rated kVA. They are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards.
Long Description	DOE 2016 Efficient Transformer, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings
Product Type	15KVA DOE2016 Eff 3PH 480-208Y/120 150C

Manufacturer Information

Brand	Eaton
GTIN	00786680147517
Manufacturers Part Number	V48M28T1516
UPC	786680147517

Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Ventilated transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	258

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional Energy
Frequency Rating	60 Hz
standard	UL Listed,DOE2016 Efficient
Temperature Rating	150 °C rise