

Specifications



Photo is representative

Eaton V48M28T7516

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR942, 220°C, 75 kVA, Floor mnt, 3-phase, PV: 480V delta, SV: 208Y/120, 50 dB, 2 at +2.5%, 4 at -2.5%, 150°C, 75 kVA, WS59, 280B

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T7516
UPC	786680147548
PRODUCT LENGTH/DEPTH	24 in
PRODUCT HEIGHT	43 in
PRODUCT WIDTH	30.5 in
PRODUCT WEIGHT	545 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient

Physical Attributes	
COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 2
FRAME	FR942
INSULATION	220 °C
MOUNTING	Floor
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated dry-type transformer
WIRING CONNECTION	280B

Miscellaneous	
WEATHERSHIELD	WS59

Performance Ratings	
EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	75 kVA
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	75 kVA
VOLTAGE RATING	480 Vac-208Y/120 Vac

Resources	
BROCHURES	Eaton's low-voltage dry-type distribution transformers Eaton's high-efficiency dry-type transformers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T7516

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton V48M28T7516

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR942, 220°C, 75 kVA, Floor mnt, 3-phase, PV: 480V delta, SV: 208Y/120, 50 dB, 2 at +2.5%, 4 at -2.5%, 150°C, 75 kVA, WS59, 280B

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T7516
UPC	786680147548
PRODUCT LENGTH/DEPTH	24 in
PRODUCT HEIGHT	43 in
PRODUCT WIDTH	30.5 in
PRODUCT WEIGHT	545 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient

Physical Attributes	
COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 2
FRAME	FR942
INSULATION	220 °C
MOUNTING	Floor
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated dry-type transformer
WIRING CONNECTION	280B

Miscellaneous	
WEATHERSHIELD	WS59

Performance Ratings	
EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	75 kVA
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	75 kVA
VOLTAGE RATING	480 Vac-208Y/120 Vac

Resources	
BROCHURES	Eaton's low-voltage dry-type distribution transformers
	Eaton's high-efficiency dry-type transformers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T7516

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

