



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



V48M28T7516 75KVA Ventd XFMR DOE2016 Eff 3PH 480-208Y/120 150C *Eaton Corp*

Catalog Number	V48M28T7516
Manufacturer	Eaton Corp
Description	Dry Type Transformer, 480 V, 208Y/120 V, 75 K Va Va Rating, Efficient Transformer, 24 In Overall Length, 30.5 In Overall Width, 43 In Overall Height, 60 HZ, 150 °C Temperature Rise Rating, 609 LB
Weight per unit	659.0 (lbs/each)
Product Category	Three Phase Energy Efficient D

Features

dimensions	24.0000 IN X 30.5000 IN X 43.0000 IN
Efficiency	10 CFR Part 431-2016 (DOE 2016)
Insulation Class	220 °C
kva rating	75 kVA
Number of Phases	Three-phase
Primary Voltage	480 V DELTA
Secondary Voltage	208y/120 V
Tap Size	2 at +2.5%, 4 at -2.5%

Descriptions

Description	75KVA VENTD XFMR DOE2016 EFF 3PH 480-208Y/120 150C
extra long description	ETN V48M28T7516 75KVA DOE2016 EFF 3
Features	Eaton types DS-3 (single-phase) and DT-3 (three-phase) general purpose ventilated dry-type transformers are two-winding, self-cooled, and available in a wide variety of primary and secondary voltage combinations. General purpose transformers are designed for continuous operation at rated kVA. They are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards.
Special Features	Fungus-resistant varnished core and coil

Manufacturer Information

GTIN	00786680147548
UPC	786680147548

Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Ventilated transformer

Packaging

Carton	1
Weight Per each	659



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyCommercial / Institutional Buildings / Structures - Power Distribution and Controls
Frequency Rating	60 Hz
Mounting standard	FLOOR UL Listed,DOE2016 Efficient
Temperature Rating	150 °C rise