



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode
79701-0000, TX Midland
Phone: 432-685-3108
Fax: 432-685-3706



TH3361 TH3361 30A 600V Fusible Type1 *Industrial Connections &*

Catalog Number	TH3361
Manufacturer	Industrial Connections &
Description	No Matter The Application, Weave Got You Covered With A Rugged, Reliable and Easy-to-Install Spec-Setter Safety Switch. 30A 3P HD N1 600V Fusible SW
Weight per unit	10,500.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	30
Poles	3
Voltage Rating	600 AC

Dimensions and Weight

Size	12.60 in
------	----------

Descriptions

Description	TH3361 30A 600V FUSIBLE TYPE1
extra long description	GE TH3361 30A 3P HD N1 600V FUSIBLE
Long Description	No matter the application, weave got you covered with a rugged, reliable and easy-to-install Spec-Setter safety switch. 30A 3P HD N1 600V FUSIBLE SW
Product Type	30A 3P HD N1 600V Fusible SW
Special Features	Designed for commercial and industrial applications where safety, high performance and continuity of service are essential. Listed to UL standard 98 enclosed and dead front switches. Suitable for use as service equipment when installed in accordance with the National Electrical Code. Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches. Meets or exceeds NEMA KS1 standard for enclosed switches, type HD. Fusible and non-fusible switches available (consult BuyLog for interrupt ratings). Qu

Manufacturer Information

Brand	GE
GTIN	00783164009095
Manufacturers Part Number	TH3361
UPC	783164009095

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
----------------------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode
79701-0000, TX Midland
Phone: 432-685-3108
Fax: 432-685-3706

Packaging

Carton	1
Weight Per each	10500

Uses, Certifications, and Standards

Application	Heavy
Enclosure standard	NEMA 1 (Indoor) Yes