

Specifications



Photo is representative

Eaton VMVL-7-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 129 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 57W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-7-UNV1
UPC	662276861015
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Resources

3D MODELS	SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures
BROCHURES	Crouse-Hinds series DLC approved lighting products Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure Crouse-Hinds series Global LED lighting portfolio
CATALOGS	Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page
INSTALLATION INSTRUCTIONS	IF 1888 - Champ VMVL and PVML Driver Replacement IF 1882 - Champ VMVL and PVML LED luminaires
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - VMVL-7-UNV1 Champ VMV LED Hazardous Area

Product specifications

LUMENS	7000
LUMENS PER WATT	129
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	No mounting module
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	57W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	175W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton VMVL-7-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 129 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 57W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-7-UNV1
UPC	662276861015
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Resources

3D MODELS	SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures
BROCHURES	Crouse-Hinds series DLC approved lighting products Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure Crouse-Hinds series Global LED lighting portfolio
CATALOGS	Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page
INSTALLATION INSTRUCTIONS	IF 1888 - Champ VMVL and PVML Driver Replacement IF 1882 - Champ VMVL and PVML LED luminaires
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - VMVL-7-UNV1 Champ VMV LED Hazardous Area

Product specifications

LUMENS	7000
LUMENS PER WATT	129
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	No mounting module
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	57W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	175W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.