



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THQL1130 1P 30A 120/240V Circuit Breaker

*Industrial Connections &*

|                  |  |
|------------------|--|
| Catalog Number   | THQL1130   |
| Manufacturer     | Industrial Connections &   |
| Description      | Q Line Circuit Breakers Are One-Inch Wide Per Pole, Compact, Thermal-Magnetic Devices Designed For Residential and Commercial Applications In Load Centers or Lighting Panels. All Q Line Circuit Breakers Feature Quick-Make / Quick-Break Mechanisms, Common Trip Bars, and Easy to Spot Trip Indication to Ensure Safety and Reliability. Q Line Breakers Can Be Ordered With Auxiliary Contact and Shunt Trip Accessories, and Can Be Ordered For Use In Hid Applications. The THQL1130 Breaker Features 1 Pole, An Ampere |
| Weight per unit  | 312.0 (lbs/each)   |
| Product Category | 1 Pole Standard Trip Plug-In   |

### Features

|                      |                                 |
|----------------------|---------------------------------|
| amperage rating      | 30 A                            |
| circuit breaker type | Residential                     |
| frame                | Q-Line                          |
| interrupt rating     | 10kA@120 Vac / 10kA@120/240 Vac |
| Load Rating          | HACR                            |
| media                | Yes                             |
| Poles                | 1                               |
| trip range           | Non-Interchangeable             |
| Trip Type            | LI                              |
| Voltage Rating       | 120/240 V                       |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 1P 30A 120/240V CIRCUIT BREAKER  |
| extra long description | GE THQL1130 THQL 1 POLE 120/240V 10  |
| Long Description       | Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL1130 breaker features 1 pole, an ampere |
| Product Type           | THQL 1 Pole 120/240V 10K Ic 30amp  |
| Special Features       | Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL1130 breaker features 1 pole, an ampere |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | GE             |
| GTIN                      | 00783164012873 |
| Manufacturers Part Number | THQL1130       |
| sub brand                 | Q Line         |
| UPC                       | 783164012873   |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Loadcenter Plug In Breakers and Accessories |
| Type                 | Q-Line Plug-In                              |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 10  |
| Package         | 1   |
| Weight Per each | 312 |

## Uses, Certifications, and Standards

|             |                  |
|-------------|------------------|
| Application | Thermal Magnetic |
| standard    | E11592           |