

FEATURES & SPECIFICATIONS

PRODUCT OVERVIEW

Ideal for entrances, stairwells, corridors and other pedestrian areas.

CONSTRUCTION

Finish is dark bronze.

WC: Rugged, corrosion-resistant, die-cast aluminum back housing and hinged door frame. Four 1/2" conduit hubs.

W: Cast aluminum backplate with a polycarbonate cover. Designed for wall mounting and includes two 3/4" knockouts for routing electrical conduit.

ELECTRICAL SYSTEM

Medium-base lamp included.

WC: Quad-tap, high-reactance, high power factor ballast.

W: 120V, normal power factor ballast.

LISTINGS

Listed and labeled to UL standards for wet locations.

Listed and labeled to CSA standards.

25°C maximum ambient temperature.

WARRANTY

Fixtures are covered by Lithonia Lighting 24-month warranty against mechanical defects in manufacture.

Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

Contractor Select

Building Mounted


70 - 100W




W70



WC100



W70



WC100

ORDERING INFORMATION

Catalog Number	UPC	Description	Wattage	Lamp Source	Voltage	Finish	Photocell Included	Lamp Included	Weight (lbs.)	Pallet Qty.	Standard Carton Qty.
W70SPL 120 M6	745973505571	Non-cutoff	70	HPS	120	Dark Bronze	Y	Y	5	144	6
WC100ML M4	745974487302	Cutoff	100	MH	120/208/240/277	Dark Bronze	N	Y	10	80	4

