



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3425IV RJ25 Conn Iv (M20)

Pass & Seymour/Legrand

Catalog Number	WP3425IV
Manufacturer	Pass & Seymour/Legrand
Description	This High-Quality RJ25 (6P6C) Keystone Connector Is Designed For Use In Any Keystone Wall Plate. It Features Rear Retention Caps To Ensure Secure Wire Termination, Making It A Reliable Choice For Your Network Setup.
Weight per unit	0.0321 (lbs/each)
Product Category	Outlets, Jacks, & Plates

Features

connection	RJ25 Female
insulation	Insulation Resistance: > 10
Resistance	500 (@ 100 VDC)

Material, Color, and Finish

Color	Ivory
Finish	Smooth plastic

Dimensions and Weight

Size	1.1 x 0.67 x 0.87 (27.95 x 16.90 x 22)
------	--

Descriptions

Description	RJ25 CONN IV (M20)
extra long description	OnQ WP3425IV RJ25 CONNECTOR IVORY (
Features	This high-quality RJ25 (6P6C) Keystone Connector is designed for use in any Keystone wall plate. It features rear retention caps to ensure secure wire termination, making it a reliable choice for your network setup.
Long Description	This high-quality RJ25 (6P6C) Keystone Connector is designed for use in any Keystone wall plate. It features rear retention caps to ensure secure wire termination, making it a reliable choice for your network setup.
Product Type	RJ25 Connector Ivory (M20)
Special Features	Quick Connect

Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428024996
Manufacturers Part Number	WP3425-IV
UPC	804428024996



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	RJ25 6-Position, 6-Conductor Telephone connector

Packaging

Carton	20
Package	120
Weight Per each	0.0321

Uses, Certifications, and Standards

Application	Residential
Enclosure	High Impact Flame Retardant Plastic
environmental conditions	10 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	CSA, cULus, RoHS
Temperature Rating	-10 to 60 F (-23.33 to 15.56 C)