



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TLP76BUC Tripp Lite 7-Outlet Surge Protector, 1500 Joules *Eaton Power Quality*

Catalog Number	TLP76BUC
Manufacturer	Eaton Power Quality
Description	Protect It! 7-Outlet Surge Protector - 5-15R Outlets, 1500 Joules, 2 Usb Charging Ports, 6 FT. (1.8 M) Cord, Black
Weight per unit	N/A
Product Category	20260619091902

Features

Input Voltage	120V AC
nominal voltage	120V AC
Number of Outlets	(7) 5-15R
Outlet	NEMA 5-15P
Plug Type	NEMA 5-15P
Voltage Rating	120V AC V
Wattage	1800 W

Dimensions and Weight

Depth	13.900
Height	1.18
Width	2.17

Descriptions

Description	TRIPP LITE 7-OUTLET SURGE PROTECTOR, 1500 JOULES
extra long description	TRIPP TLP76BUC TLP76BUC
Long Description	Protect It! 7-Outlet Surge Protector - 5-15R Outlets, 1500 Joules, 2 USB Charging Ports, 6 ft. (1.8 m) Cord, Black
Product Type	Tlp76buc
Special Features	7-Outlet Surge Protector Safeguards Your Sensitive ElectronicsIdeal for your home, office or retail workstation, this Protect It!® surge protector features a surge protection rating of 1500 joules to defend your valuable electronic components against power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP76BUC protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G). NEMA 5-15R Outlets Accept

Manufacturer Information

Brand	Eaton Power Quality
Manufacturers Part Number	TLP76BUC



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
--------	---

Weight	1.000 LB
--------	----------

Weight Per each	0
-----------------	---

Uses, Certifications, and Standards

Application	Home/Office/Business
-------------	----------------------

Frequency Rating	50 / 60 Hz
------------------	------------

Mounting	1
----------	---

Operating Temperature	32° to 104°F (0° to 40°C)
-----------------------	---------------------------

standard	Exceeds IEEE 587 category A&B specifications
----------	--

Temperature Rating	32° to 104°F (0° to 40°C)
--------------------	---------------------------