



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105  
78653-0000, TX Manor  
Phone: 512-339-8750  
Fax: 512-339-6732



## WP820 WP820 2W-3P Plug

*Crouse-Hinds*

Catalog Number	WP820
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series WP Plug, 15A, Two-Wire, Three-Pole, Copper-Free Aluminum, 5-15P, 0.500-0.625" Cord Diameter, 125 Vac
Weight per unit	0.3600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	15
Cord Type	0.500 To 0.625 In Diameter
dimensions	3.5000 IN X 2.5000 IN X 2.5000 IN
Material	Copper-Free Aluminum
Poles	3
Voltage Rating	125 V

### Descriptions

Description	WP820 2W-3P PLUG
extra long description	CRS-H WP820 WP PLUG-FS-FD-DS-S
Features	Crouse-Hinds series FS and FD device boxes are installed in non-hazardous area conduit systems to accommodate wiring devices, act as pull boxes or provide openings for taps and splices. They are suitable for use in wet locations when used with gasketed covers. FS and FD device boxes are available in two box depths with a wide variety of gang configurations, hub configurations and hub sizes. They are manufactured in cast iron, aluminum, stainless steel and malleable iron. Malleable iron boxes are also a
Long Description	Eaton Crouse-Hinds series WP plug, 15A, Two-wire, three-pole, Copper-free aluminum, 5-15P, 0.500-0.625" cord diameter, 125 Vac
Product Type	WP Plug-FS-FD-DS-S

### Manufacturer Information

Brand	Eaton
GTIN	00782274732404
Manufacturers Part Number	WP820
UPC	782274732404



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105  
78653-0000, TX Manor  
Phone: 512-339-8750  
Fax: 512-339-6732

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	PLUG

## Packaging

Carton	1
Package	5
Weight Per each	0.36

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 498, UL 514A