



TMC7247 2-1/2" Cord Grips

Crouse-Hinds

Catalog Number	TMC7247
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series TMC Cable Gland, Metal-Clad, Teck Corrugated or Interlocked Steel, or Aluminum, Armoured, Aluminum, Outer Sheath: 1.99-2.72", General Purpose, 2-1/2" NPT, Armor Range: 1.93-2.47"
Weight per unit	5.0 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Male NPT
dimensions	6.1900 IN X 4.0000 IN X 4.0000 IN
Material	Aluminum Body, Neoprene Seal

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Description	2-1/2" CORD GRIPS
extra long description	CRS-H TMC7247 2 1/2 AL FT MC CAB AR
Features	For use with metal-clad cable, TECK corrugated cable or interlocked steel or aluminum cable, Crouse-Hinds series TMC cable glands provide a means for terminating at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution equipment. TMC cable glands form a mechanical watertight connection and may be installed in Class I, Division 2 locations provided there are no arcing and sparking risks in accordance with NEC501.10B.
Long Description	Eaton Crouse-Hinds series TMC cable gland, Metal-clad, TECK corrugated or interlocked steel, or aluminum, Armoured, Aluminum, Outer sheath: 1.99-2.72", General purpose, 2-1/2" NPT, Armor range: 1.93-2.47"
Product Type	2 1/2 AL FT MC Cab Armor Od 1.93-2.47
Special Features	Weight 25 Lb per 100

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274414614
Manufacturers Part Number	TMC7247
UPC	782274414614



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10650 West Airport Suite 100
77477-0000, TX Stafford
Phone: 281-879-4911
Fax: 281-879-8596

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Weight Per each	4.993

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	IP56
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 60 Deg C