

# Eaton TMCX165 BR NP

Catalog Number: TMCX165 BR NP

Eaton Crouse-Hinds series TMCX cable gland, Metal-clad corrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Nickel-plated brass, Outer Sheath: 0.49-0.78", 1/2" NPT, Armor Range: 0.44-0.65"



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMCX cable gland	TMCX165 BR NP
	UPC
	782274172026
Product Length/Depth	Product Height
3.38 in	1.38 in
Product Width	Product Weight
1.38 in	0.78 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

### NEMA Rating

4

## Product specifications

### Protection type

Explosion-proof

### Cable type

TECK armoured

Metal-clad with interlocked or continuously welded corrugated armoured

Tray cable

### Gland type

Armoured Barrier and Non-armoured Barrier

### Material

Nickel plated brass

### Thread Size

1/2"

### Thread type

NPT

### Armor (min/max)

0.44-0.65"

### Outer sheath (min/max)

0.49-0.78"

## Resources

### Catalogs

[Crouse-Hinds series TMCX catalog page](#)

### Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

### Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

### Specifications and datasheets

[Eaton Specification Sheet - TMCX165 BR NP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)