



WEATHER-RESISTANT COMMERCIAL GRADE RECEPTACLES, IVORY

WR20TRI | Pass & Seymour

FEATURES & BENEFITS

Weather-Resistant Commercial Grade Receptacles, 20 amp, 125 volts, Ivory, WR20TRI

- Auto-ground clip assures positive ground.
- WR marking on face as required by UL Standard.
- Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Tri-drive brass terminal screws. Internal screwpressure plate back and side wire capability. Two back wire holes for more wiring flexibility.
- Heavy-duty, brass strap for added strength and ground conductivity.
- UV-resistant nylon face for longer life under adverse environmental conditions.
- Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory

Type: Receptacles

Features: Weather-Resistant

Number Of Poles: 2 Number Of Wires: 3

Special Features: Weather-Resistant, Tamper-Resistant

Style: Duplex

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes UL Listing No: UL498 UL Standard: Yes UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.130" Height (US): 3.281" Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125V Volts (AC): 125 Capacity: Duplex

Grade Type: Commercial

BUY AMERICAN ACT COMPLIANCE

Buy American Act Status: Trade Agreement Act Compliant