Specifications



Photo is representative





Eaton TMR5Y05120

TMR5 Series Time Delay Relays, Octal style terminals, 8 pins, Repeat cycle (ON time first followed up off time and repeating), 0.1-10 sec time delay, 120 Vac/dc input voltage, 10A max. allowable load, DPDT contact configuration

General specification	S
PRODUCT NAME	Eaton timing relay
CATALOG NUMBER	TMR5Y05120
UPC	786685124926
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	2.4 in
PRODUCT WIDTH	1.7 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	Eaton Selling Policy 25- 000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed (when used with Eaton socket) cRUus
CATALOG NOTES	Fixed time delay settings are available for orders of 50 pieces or more. Contact EatonCare for additional information at 877-ETN-CARE (386-2273). Dual knob unit with independently selectable/adjustable ON/OFF times.



Product specifications		
TYPE	Timing relay	
PROD LOAD	10A	
NUMBER OF PINS	8	
OPERATING MODE	Repeat cycle (ON time first followed up off time and repeating)	
CONTACT CONFIGURATION	DPDT	
SERIES	TMR5	
DIELECTRIC STRENGTH	2000 V between poles	
INPUT VOLTAGE	120 Vac/dc	
TERMINALS	Octal	
TIME DELAY	0.1-10 seconds	

Resources	
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	TMR5Y05120

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com



information.



latest product and support

Follow us on social media to get the



