

# Specifications



Photo is representative

## Eaton TR1877LABXSP

Eaton commercial specification grade single receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Side wire, Light almond, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Single, Screw, PVC, ED Box

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial specification grade single receptacle
<b>CATALOG NUMBER</b>	TR1877LABXSP
<b>UPC</b>	032664750212
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	0.87 in
<b>PRODUCT WEIGHT</b>	0.155 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	Commercial specification grade



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Receptacle
<b>TYPE</b>	Single receptacle
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	125V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Auto-grounding Tamper resistant
<b>APPLICATION</b>	Commercial
<b>DEVICE GRADE</b>	Commercial
<b>WIRING METHOD</b>	Side wire
<b>NUMBER OF WIRES</b>	3
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Standard
<b>MATERIAL</b>	PVC
<b>PACKAGING TYPE</b>	ED Box
<b>COLOR</b>	Light almond
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	Side Wiring: #10-14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-20R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	PVC body Impact-resistant thermoplastic face
<b>RECEPTACLE TYPE</b>	Single

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Resources

MULTIMEDIA	<a href="#">Residential straight blade receptacles</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TR1877LABXSP</a> <a href="#">Commercial grade straight blade duplex receptacles spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

