



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XHHW2501000 AI XHHW 250 STR BK 1000

King Wire Inc.

Catalog Number	XHHW2501000
Manufacturer	King Wire Inc.
Description	Aluminum Building Wire, 600 V, 22 Strands, 250 Kcmil Conductor Size, Xlpe Insulation Material, Black, 1000 FT Overall Length, 653 Mil Outside Diameter, 55 Mil Insulation Thickness, +90 °C Operating Temperature, 296 LB/MFT
Weight per unit	0.2960 (lbs/ft)
Product Category	XHHW-STR (Stranded)

Features

Stranding	22 STRANDS
-----------	------------

Material, Color, and Finish

Insulation Color	BLACK
------------------	-------

Dimensions and Weight

Length	1000 FT
Length in ft	1000 watt
Outer Diameter	653 MIL

Descriptions

Commodity Description	ALUMINUM BUILDING WIRE-XHHW-STR
Description	AL XHHW 250 STR BK 1000

Manufacturer Information

GTIN	00032886542466
UPC	032886542466

Taxonomies, Classifications, and Categories

Category Description	ALUM BUILDING WIRE
Type	XHHW-2

Packaging

Carton	1000
Weight Per foot	0.296

Uses, Certifications, and Standards

Approval	UL 44
Temperature Rating	90 DEG C

SIMpull XHHW-2®

Aluminum XHHW Wire & Cable



600 Volt Alumaflex® Brand Aluminum Alloy (AA-8176) Conductor. Cross-linked Polyethylene (XLPE) Insulation. Moisture Resistant High Heat. Sunlight Resistant in Sizes 6 AWG and Larger. CT Rated in Sizes 1/0 AWG and Larger.

APPLICATIONS

Southwire SIMpull XHHW-2® aluminum conductors are primarily used in conduit or recognized raceways for service and feeder wiring as specified in the National Electrical Code. XHHW-2 conductors may be used in wet or dry locations at temperatures not to exceed 90°C. Voltage rating for XHHW-2 conductors is 600 volts. Suitable for use in Health Care Facilities per section 517.160 of the NEC where a dielectric constant of 3.5 or less may be specified. This product is designed to be installed without the application of pulling lubricant.

STANDARDS & REFERENCES

Southwire Aluminum Type XHHW-2 conductors comply with the following:

- ASTM- All Applicable Standards
- UL Standard 44
- NOM-ANCE 90° C
- Federal Specification A-A-59544
- National Electrical Code, NFPA 70
- NEMA WC-70 (ICEA S-95-658) Construction Requirements
- RoHS/Reach Compliant

CONSTRUCTION

Southwire Type XHHW-2 aluminum conductors are Alumaflex® brand AA-8000 series aluminum alloy, compact stranded. The insulation is an abrasion, moisture and heat resistant SIMpull® thermoset cross-linked polyethylene. Conductor sizes 6 AWG and larger are listed and marked sunlight resistant in all colors. Available in black, white, red, blue, brown, orange, yellow, purple, gray, and green. Some colors are subject to economic order quantity.



Revised March 12, 2018

The Power of Connections.™

©2015 Southwire Company, LLC. All rights reserved. ®Registered Trademark and ™Trademark of Southwire Company, LLC.
One Southwire Drive, Carrollton, GA 30119, USA



Conductor		Insulation Thickness (mils)	Nominal O.D. (mils)	Approx. Net Wt. Per 1000' (lbs.)	Allowable Ampacities+			Standard Package
Size (AWG or kcmil)	No. of strands				60°C	75°C	90°C	
8	7	45	227	30	35	40	45	BCD
6	7	45	259	39	40	50	55	BCD
4	7	45	303	57	55	65	75	BCD
2	6	45	358	85	75	90	100	BCD
1	8	55	413	108	85	100	115	BC
1/0	10	80	450	180	115	135	150	ABC
2/0	12	55	490	161	115	135	150	ABCD
3/0	16	55	537	198	130	155	175	BCD
4/0	19	55	589	243	150	180	205	ABCD
250	22	55	650	293	170	205	230	BCD
300	35	65	700	346	195	230	260	BC
350	35	65	746	398	210	250	280	BCD
400	35	65	789	449	225	270	305	CD
500	35	65	866	552	260	310	350	ABCDE
600	58	80	973	675	285	340	385	ABD
700	58	80	1037	777	315	375	425	N/A
750	58	80	1068	829	320	385	435	ABCE
900	58	80	1162	979	355	425	480	N/A
1000	58	80	1220	1085	375	445	500	C
<p>+ Allowable Ampacities shown are for general use as specified by the National Electrical Code, Sections 310.15 and 240.4(D). Unless the equipment is marked for use at higher temperatures, the conductor ampacities shall be limited to the following per NEC 110.14(C): 60°C - When terminated to equipment for circuits rated 100 amperes or less marked for 14 through 1 AWG conductors. 75°C - When terminated to equipment for circuits rated over 100 amperes or marked for conductors larger than 1 AWG. 90°C - THHN dry locations and THWN wet or dry locations for ampacity adjustment purposes using NEC section 310.15.</p>								<p>Package Codes A-500' B-2,500' C-1,000' D-5,000'</p>

RECOMMENDED SAMPLE SPECIFICATIONS:

Conductors shall be UL-listed Type XHHW-2, suitable for operation at 600 volts or less in wet or dry locations at temperatures not to exceed 90 °C. Conductors shall be annealed Alumaflex® brand aluminum alloy as manufactured by Southwire Company or approved equal.

Revised March 12, 2018

The Power of Connections.™



Conductor		
Size (AWG or kcmil)	No. of strands	Stock Numbers
8	7	Stock #: N/A
6	7	Stock #: BK:112706, BN:591209, OE:591210, YW:591211, GN:585321
4	7	Stock #: BK:112714, RD:591114, BE:591115, WE:591116, BN:591201, OE:591202, YW:591203, GN:585320
2	7	Stock #: BK:112722, BN:591213, OE:591214, YW:591215, GN:585319
1	18	Stock #: BK:112730, RD:591204, BE:591205, WE:591206, BN:591207, OE:591208, YW:591216, GN:585318, GY:596497
1/0	18	Stock #: BK:112748, RD:591284, BE:591285, WE:591286, BN:585291, OE:585292, YW:585293, GY:585294, GN:585290, PE:596423
2/0	18	Stock #: BK:112755, RD:591288, BE:591289, WE:591290, BN:585296, OE:585297, YW:585298, GY:585300, GN:585295, PE:596422
3/0	18	Stock #: BK:112763, RD:585302, BE:585303, WE:585304, BN:585305, OE:585306, YW:585308, GY:585309, GN:585301, PE:596421
4/0	18	Stock #: BK:112771, RD:585317, BE:585316, WE:585314, BN:585313, OE:585312, YW:585311, GY:585310, GN:567439, PE:592563
250	22	Stock #: BK:278341, RD:576390, BE:576391, WE:576392, BN:576385, OE:576386, YW:576387, GY:576388, GN:567440, PE:592468
300	35	Stock #: BK:278358, RD:576382, BE:576383, WE:576384, BN:576133, OE:576134, YW:576135, GY:576136, GN:576361, PE:593380
350	35	Stock #: BK:278366, RD:576378, BE:576379, WE:576380, BN:576374, OE:576375, YW:576376, GY:576377, GN:567437, PE:592562
400	35	Stock #: BK:278374, RD:576370, BE:576372, WE:576373, BN:576127, OE:576129, YW:576130, GY:576131, GN:567384, PE:593379
500	35	Stock #: BK:278382, RD:576367, BE:576368, WE:576369, BN:576362, OE:576364, YW:576365, GY:576366, GN:576394, PE:589196
600	58	Stock #: BK:278390, RD:576350, BE:576351, WE:576352, BN:576345, OE:576346, YW:576347, GY:576349, GN:567375, PE:589197
700	58	Stock #: BK:278408, RD:591293, BE:591294, WE:591295, BN:576341, OE:576342, YW:576343, GY:576344, GN:591296
750	58	Stock #: BK:278416, RD:592233, BE:592234, WE:592235, BN:567432, OE:567433, YW:567434, GY:567435, GN:567436, PE:592469
900	58	Stock #: BK:554059, BN:560445, OE:560446, YW:560447, GY:560448, PE:596424
1000	58	Stock #: BK:278424
Color Abbreviations BK-Black RD- Red BE-Blue WE-White BN-Brown OE-Orange YW- Yellow GY-Grey GN-Green PE-Purple		

Revised March 12, 2018

The Power of Connections.™



Southwire®