




Pass & Seymour

Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V

TR5251, TR5351

Rugged construction plus tamper-resistance equals one safe receptacle


Tamper-resistant child safety outlets that conform to 2008 NEC® Article 406.11 are now available as a specification grade single receptacle. The sturdy mechanical shutter system helps prevent children from inserting foreign objects into the receptacle. Corrosion-resistant plated steel straps, rugged nylon faces and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable long-term performance. Tri-drive mounting and backed out terminal screws combine to save installation time.



Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

One-piece brass triple-wipe power contacts for lasting retention.



Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

TR5351-LA

Field Uses/Vertical Markets

■ Retail

■ Office

■ Hospitality/Lodging

■ Multiple Dwelling

SF312R1 — Updated March 2008 — For latest specs visit www.legrand.us/passandseymour



Pass & Seymour

Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V

Ordering Information

Catalog Number	Rating		Color	NEMA Config. No.
	A.	V.		
Single Receptacles Back & Side Wire				
TR5251-I	15	125	Ivory	5-15R
TR5251-W	15	125	White	5-15R
TR5251	15	125	Brown	5-15R
TR5251-LA	15	125	Light Almond	5-15R
TR5351-I	20	125	Ivory	5-20R
TR5351-W	20	125	White	5-20R
TR5351-LA	20	125	Light Almond	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

SF312R1 — Updated March 2008 — For latest specs visit www.legrand.us/passandseymour

Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V



Pass & Seymour

Technical Specifications


3rd Party Compliance

UL Listed, File Number E140596, Standard UL498; Federal Specification WC596; CSA Certified, Standard CSA-C22.2 No. 42.



Performance

Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 - #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2



**Dimensions for
15 & 20 Amp**


Materials

Face	Nylon	Terminal Screws	Tri-Drive Brass
Back Body	PVC	Hex Head Grounding Screw	Tri-Drive Zinc
Contacts	.032 (.8) Brass		Plated Steel
Clamping Plate	.080 Steel	Assembly Rivets	Steel
Mounting Strap	.042 Steel	Mounting Screws	Tri-Drive Steel

Warranty


1Year

Complementary Devices & Accessories




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Lighting & Fan Controls
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca




Pass & Seymour

Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V

TR5251, TR5351

Rugged construction plus tamper-resistance equals one safe receptacle


Tamper-resistant child safety outlets that conform to 2008 NEC® Article 406.11 are now available as a specification grade single receptacle. The sturdy mechanical shutter system helps prevent children from inserting foreign objects into the receptacle. Corrosion-resistant plated steel straps, rugged nylon faces and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable long-term performance. Tri-drive mounting and backed out terminal screws combine to save installation time.



Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

One-piece brass triple-wipe power contacts for lasting retention.



TR5351-LA

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

Field Uses/Vertical Markets

■ Retail

■ Office

■ Hospitality/Lodging

■ Multiple Dwelling

SF312R1 — Updated March 2008 — For latest specs visit www.legrand.us/passandseymour



Pass & Seymour

Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V

Ordering Information

Catalog Number	Rating		Color	NEMA Config. No.
	A.	V.		
Single Receptacles Back & Side Wire				
TR5251-I	15	125	Ivory	5-15R
TR5251-W	15	125	White	5-15R
TR5251	15	125	Brown	5-15R
TR5251-LA	15	125	Light Almond	5-15R
TR5351-I	20	125	Ivory	5-20R
TR5351-W	20	125	White	5-20R
TR5351-LA	20	125	Light Almond	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V



Pass & Seymour

Technical Specifications


3rd Party Compliance

UL Listed, File Number E140596, Standard UL498; Federal Specification WC596; CSA Certified, Standard CSA-C22.2 No. 42.



Performance

Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 - #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2



**Dimensions for
15 & 20 Amp**


Materials

Face	Nylon	Terminal Screws	Tri-Drive Brass
Back Body	PVC	Hex Head Grounding Screw	Tri-Drive Zinc
Contacts	.032 (.8) Brass		Plated Steel
Clamping Plate	.080 Steel	Assembly Rivets	Steel
Mounting Strap	.042 Steel	Mounting Screws	Tri-Drive Steel

Warranty


1Year

Complementary Devices & Accessories




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Lighting & Fan Controls
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca