



HOSPITAL-GRADE TAMPER-RESISTANT COMPACT DESIGN RECEPTACLE, BACK & SIDE WIRE, 20A, 125V, WHITE

TR8300HW | Pass & Seymour

FEATURES & BENEFITS

Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back & Side Wire, 20amp, 125volt, White

For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

- Impact-resistant nylon face.
- One-piece heat-treated triple-wipe brass power contacts.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Corrosion-resistant, zinc-plated steel strap is locked in.
- Internal screw-pressure-plate back wire and side wire line terminals accept #14 #10 AWG copper or copper-clad conductors.
- · High strength thermoplastic back body.
- · Auto-ground clip assures positive ground.
- · Compact design for easy installation.
- Tri-drive terminal and mounting screws.
- Meets National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- .032-inch thick brass, triple-wipe power contacts for lasting retention.
- Terminal compartments isolated from each other for positive conductor containment.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Compact Design, Receptacles

Duty: Heavy Duty

Special Features: Back, Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes Federal Spec: Yes UL Listing No: UL498 UL Standard: Yes UN SPSC: 39121406

UR: No

DIMENSIONS

Depth (US): .780" Height (US): 3.281" Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 20A

NEMA Rating: 5-20R

Volts: 125V Volts (AC): 125 Capacity: Duplex Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

