HellermannTyton

Specification Sheet

Part Number: TSR3I-50

Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.

PVC construction is lightweight, durable and more affordable than metallic raceway systems.

Flexible hinge is designed to reduce stress cracking and discoloration from repeated opening and closing.

Systems and fittings are available in white, office white and ivory to coordinate with a variety of décor.

Fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.



Ceiling Drop, 1-3/4", 2-Piece, PVC, Ivory, 10 Individual/bag

Article Number 250-03501

Type TSR3-50

Color Ivory (IV)

Quantity Per bag

Product Description

HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. TSR surface raceway systems can be used to route a variety of communication cable, including high speed UTP and fiber optic cable.

Short Description

Ceiling Drop, 1-3/4", 2-Piece, PVC, Ivory, 10 Individual/bag

Global Part Name

TSR3-50-PVC-BGE

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

UL 94 V-0

Halogen Free

No

Operating Temperature

+122°F (+50°C)

Reach Compliant (Article 33)

No

ROHS Compliant

Yes

Package Quantity (Imperial)

10

| Package Quantity (Metric) | 10 | | |
|---|-------------------------------------|------------|----------------------|
| Customs Number | 3925900000 | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| © 2023 HellermannTyton. All Rights Res Conta | served. act Us RoHS/WEEE Compliance | Disclaimer | Terms and Conditions |
| | | | |
| | | | |
| | | | |