# Universal toggle dimmer

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:



### **Description**

Single-pole & 3-way 300W Dimmable LED, Dimmable Compact Fluorescent (CFL) 600W/VA Incandescent (INC)/Halogen (HAL), Dimmable Fluorescent (FLR), Magnetic Low-Voltage (MLV), Electronic Low-Voltage (ELV)

#### **Design features**

- Preset feature allows user to return to previous light level when turning lights ON
- Integrated full-slide control for easy, precise operation
- Device can be wired into either 3-way location (load side or line side)
- · Neutral is not required for installation of device
- · Adjustable low-level trim setting for optimal lamp compatibility
- · Faceplate is removable to allow for color changes
- · Radio frequency interference filtering is standard on all models
- Electrostatic discharge protection
- Compatible with any traditional toggle wallplate or screwless toggle wallplate
- Compatible with most common dimmable lighting loads (Forward phase-cut)
- Color change kits are available with packout of 3 different colors for increased flexibility and convenience
- Soft gradual ON feature
- · California Title 20/24 compliant

Table 1. Universal Toggle Dimmer, Back & Side Wire

		Compatible	Rating		
Catalog No.	Description	Lamp Types	Watt	V/AC	Color Suffix
□ TUL06P	Universal toggle dimmer single pole/3-way	Dimmable LED/CFL	300	120	C2, C7
	preset, back and side wire	INC, HAL, FLR, MLV, ELV	600	120	C2, C7
□ TCK3	Color change faceplate for TUL06P	_	_	_	B, BK, GY, LA, V, W

Compliances, specifications and availability are subject to change without notice.



	Project Name:	Prepared By:		
	Project Number:	Date:		
	Catalog Number:	Type:		

## **Applications**

The universal toggle dimmer offers a traditional toggle look with integrated full-range dimming for 300W dimmable LED and CFL as well as 600W incandescent, halogen, dimmable fluorescent, electronic low-voltage & magnetic low-voltage light sources. These units are ideal for residential and light commercial applications and are compatible with Eaton's Wiring Devices traditional toggle style devices and wallplates. The preset feature automatically returns light(s) to the previous setting. The device is designed for both single pole (one location) and 3-way (multi-location) applications, and features a soft gradual ON setting that provides seamless dimming.

Table 2. Specifications


Catalog No.	TUL06P, TCK3 Series			
Device Type	Universal Toggle Dimmer			
Wiring Type	Back & side wire			
Testing & Code Compliance	cULus Listed to UL1472, file no. E47967     NOM Certified     California Title 20/24 compliant			
Environmental Specifications	Flammability: Meets UL 94 requirements; V2 rated Temperature Rating: -20°C to 70°C (-4°F to 158°F)			
Electrical Specifications	Rating: 120V/AC 60 Hz Light Intensity Control: Full-range, continuously variable dimming Dimming Performance: Solid State Dimming Radio Frequency Interference: Designed to reduce interference with radio, audio and video equipment Power-failure Memory: Light returns to same level prior to power interruption Lamp Ratings: 300W dimmable LED/CFL 600W incandescent, halogen, dimmable fluorescent, electronic low-voltage, magnetic low-voltage			
Mechanical Specifications	Wiring Types: Single pole & 3-way Voltage Ratings: Permanently marked on device			
Table 3. Materials				
Catalog No.	TUL06P, TCK3 Series			
Top Housing	Polycarbonate			
Bottom Housing	Polycarbonate			
Strap	Aluminum			
Form Factor	Decorator			
Finish	Gloss			

Table 4. De-Rating Chart - 600W Models

Lamp Type	1-Gang	2-Gang	3-Gang +
LED/CFL	300W max.	300W max.	300W max.
INC, HAL, ELV	600W max.	600W max.	600W max.
MLV	600VA max.	600VA max.	600VA max.
FLR	600W max.	600W max.	600W max.

## Table 5. Color Ordering Information

For ordering devices, include Catalog no. followed by the Color suffix: C2 (Color Change Kit: LA, W, V), C7 (Color Change Kit: B, BK, GY)



#### Table 6. Quick Compatibility Guide

Refer to www.Eaton.com/led-dimming

	Project Name:	Prepared By:		
	Project Number:	Date:		
	Catalog Number:	Type:		

#### **Product Dimensions**





Figure 1. TUL06P Line Art With Dimensions

## **Certifications & Compliances**

Catalog No		c(UL) us	NOM 426	717L 20/2	E 44		
TUL06P		•	•	•			
TCK3		•	•	•		-	
KEY:	c (UL) us	cULus		NOM 426	NOM	7 (TLE 20/24	TITLE 20/24


## **Wiring Diagrams**

Single Pole Wiring Diagram INC, HAL, LED/CFL, FLR, MLV, ELV



Note: Location of terminal screws are color-coded with "BK" or "YL"

#### 3-Way Wiring Diagram INC, HAL, LED/CFL, FLR, MLV, ELV



Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com/wiringdevices

Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada EatonCanada.ca Eaton.com/wiringdevices

Eaton.com/wiringdevices

Cerrada 8 de Mayo Cuautitlan, Mexico CP 54800

Electrical Sector

Mexico Operations

Col. Villa Jardin esq.

Eaton.mx

Carr. Tlalnepantla -Cuautitlan Km 17.8 s/n



Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

© 2020 Eaton All Rights Reserved Printed in USA Publication No. TD610116EN March 2020