



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street  
72701-0000, AR Fayetteville  
Phone: 479-443-4948  
Fax: 479-443-6465



## UAG212 2-1/2" Ua Sealtite Conduit, Bonded UI 25' *Southwire Company*

Catalog Number	UAG212
Manufacturer	Southwire Company
Description	TITAN2 Type UI LFMC Is Manufactured With A Spiral Wound Strip Of Heavy Gauge Corrosion-Resistant Hot-Dipped Galvanized Steel. For 3/8" Through 1-1/4" Trade Sizes The Core Is Constructed With A Square Locked Steel Strip With An Integral Copperbonding Strip Enclosed Within The Steel Convolutions. For 1-1/2" Through 4" Trade Sizes The Core Is Constructed With A Fully Interlocked Steel Strip. A Rugged Flame Retardant Flexible PVC Jacket Is Extruded Over The Steel Core. The Grey Jacket Resists Oils Mild
Weight per unit	2.0 (lbs/each)
Product Category	Conduit & Raceways

### Descriptions

Description	2-1/2" UA SEALTITE CONDUIT, BONDED UL 25'
extra long description	SWC 55106401 LTM-UL 2-1/2" GYJT 25C
Long Description	Titan2 Type UL LFMC is manufactured with a spiral wound strip of heavy gauge corrosion-resistant hot-dipped galvanized steel. For 3/8" through 1-1/4" trade sizes the core is constructed with a square locked steel strip with an integral copperbonding strip enclosed within the steel convolutions. For 1-1/2" through 4" trade sizes the core is constructed with a fully interlocked steel strip. A rugged flame retardant flexible PVC jacket is extruded over the steel core. The grey jacket resists oils mild
Product Type	LTM-UI 2-1/2" Gyjt 25CN
Short Description	2" TITAN METAL-FLEX CONDUIT TY

### Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886043000
Manufacturers Part Number	55106401
UPC	032886043000

### Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

### Packaging

Carton	25
Weight Per each	1.97