

## UG5 Ultra GLIDER™ Cable Pulling Lubrication System



The Greenlee UG5 Ultra Glider™ is the “new way” to effectively apply cable lube during cable installation. The Ultra GLIDER™ has several advantages over the manual method used by most contractors today.

- Applies lube more evenly around the cable and more consistently than can be done by hand. This reduces the force required by the cable puller and reduces the chance for damage to the cable.
- During a cable pull, the person feeding the cable usually can also operate the Ultra GLIDER™, which reduces the need for one person on the job.
- Eliminates the need for a person to place their hands near the point where the cable enters the conduit or duct.
- Eliminates the mess and slippery surfaces associated with manual cable lubrication.
- Applicators clean easily with water. Power unit and hose do not require cleaning between jobs.
- 3 pump speeds make it easy to match the lube rate to the needs of the pull.

CAT. NO.	UPC NO.	DESCRIPTION
UG511S	10353	ULTRA-GLIDER 120V with UGSAK slip-in applicator kit
UG511T	10355	ULTRA-GLIDER 120V with UGTAK threaded applicator kit
UG511ST	10356	ULTRA-GLIDER 120V including slip-in applicator kit UGSAK & threaded applicator kit UGTAK
UG512S	10357	ULTRA-GLIDER 12V with UGSAK slip-in applicator kit
UG512T	10359	ULTRA-GLIDER 12V with UGTAK threaded applicator kit
UG512ST	10360	ULTRA-GLIDER 12V including slip-in applicator kit UGSAK & threaded applicator kit UGTAK
UG511	10354	ULTRA-GLIDER 120V ASSEMBLY without applicators
UG512	10358	ULTRA-GLIDER 12V ASSEMBLY without applicators
UGSAK	10252	Slip-In Applicator Kit (Includes 2", 2-1/2", 3", 3-1/2" and 4" applicators with case)
UGTAK	10253	Threaded Applicator Kit (Includes 2", 2-1/2", 3", 3-1/2" and 4" applicators with case)
UGSA150	10287	<b>A</b> 1-1/2" Slip-In Applicator Assembly
UGSA200	10289	<b>A</b> 2" Slip-In Applicator Assembly
UGSA250	10291	<b>A</b> 2-1/2" Slip-In Applicator Assembly
UGSA300	10293	<b>A</b> 3" Slip-In Applicator Assembly
UGSA350	10295	<b>A</b> 3-1/2" Slip-In Applicator Assembly
UGSA400	10297	<b>A</b> 4" Slip-In Applicator Assembly
UGSA500	10304	<b>A</b> 5" Slip-In Applicator Assembly
UGSA600	10311	<b>A</b> 6" Slip-In Applicator Assembly
UGTA075	10284	<b>A</b> 3/4" Threaded Applicator Assembly
UGTA100	10285	<b>A</b> 1" Threaded Applicator Assembly
UGTA125	10286	<b>A</b> 1-1/4" Threaded Applicator Assembly
UGTA150	10278	<b>A</b> 1-1/2" Threaded Applicator Assembly
UGTA200	10279	<b>A</b> 2" Threaded Applicator Assembly
UGTA250	10280	<b>A</b> 2-1/2" Threaded Applicator Assembly
UGTA300	10281	<b>A</b> 3" Threaded Applicator Assembly
UGTA350	10282	<b>A</b> 3-1/2" Threaded Applicator Assembly
UGTA400	10283	<b>A</b> 4" Threaded Applicator Assembly
12656	12656	<b>A</b> 20' Extension Hose (MAXIMUM EXTENSION IS 20')

### SPECIFICATIONS

<b>Dimensions</b>	Depth: 17" (0.43 m) Width: 18" (0.45 m) Height: 39" (1 m)
<b>Weight</b>	24 lbs. (11 kg)
<b>Wheel Diameter</b>	8" (20 cm)
<b>Hose length</b>	10' (3 m)
<b>Battery (12V unit only)</b>	Type: Sealed lead acid rechargeable battery DC output: 12-Volt Weight: 14.5 lbs. (6.6kg) Battery Life: Three to four 5 gallon buckets per charge
<b>Motor (120V unit only)</b>	AC output: 120-Volt Amps: 6 Amps