Product specifications

Eaton E51DT5



Catalog Number: E51DT5

Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Sensor Head, E51, 0.94 in range, Top Sensing, Unshielded, Standard frequency

General specifications

Product Name
Eaton E51 NEMA limit switch inductive proximity sensor

Catalog Number
E51DT5

UPC
782113358963

Product Length/Depth
1.38 in

Product Height
1.51 in

Product Width
1.51 in

Product Weight
0.1 lb

Warranty
1 year

Certifications
UL Listed
CSA Certified

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Actuator function

Unshielded

Frequency rating

Standard

Enclosure material

Plastic

Series

E51

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Resources

Catalogs

Eaton's Volume 8—Sensing Solutions

Specifications and datasheets

Eaton Specification Sheet - E51DT5

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia