


Straight Blade Devices


TradeMaster® & Specification Grade

GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1594-I



2094-I

Features

- Meets new 2003 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: If miswired, GFCI cannot be RESET.
- Trip Indicator Light (red lamp).
- Improved resistance to surge, corrosion and electrical power line noise.
- Side or internal screw-pressure-plate back wire with #14 – #10 AWG solid or stranded copper wire.
- Line and load terminations supplied backed out and ready-to-wire.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Two back wire holes per terminal.
- Ultrasonic welding of face to back body.
- Button colors match the device face.
- Ground screw with a wire guide channel.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching nylon wall plate.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

NEW

NEW

NEW

NEW

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
TradeMaster/Spec Grade 15 Amp Duplex GFCI						
1594-I	15 125	Ivory	5-15R	•	•	•
1594-W	15 125	White	5-15R	•	•	•
1594	15 125	Brown	5-15R	•	•	•
1594-GRY	15 125	Gray	5-15R	•	•	•
1594-BK	15 125	Black	5-15R	•	•	•
1594-LA	15 125	Light Almond	5-15R	•	•	•
TradeMaster/Spec Grade 15 Amp 20 Pack Duplex GFCI						
1594-I20	15 125	Ivory	5-15R	•	•	•
1594-W20	15 125	White	5-15R	•	•	•
1594-GRY20	15 125	Gray	5-15R	•	•	•
1594-LA20	15 125	Light Almond	5-15R	•	•	•
Specification Grade 20 Amp Duplex GFCI						
2094-I	20 125	Ivory	5-20R	•	•	
2094-W	20 125	White	5-20R	•	•	
2094	20 125	Brown	5-20R	•	•	
2094-GRY	20 125	Gray	5-20R	•	•	
2094-BK	20 125	Black	5-20R	•	•	
2094-LA	20 125	Light Almond	5-20R	•	•	
Specification Grade 20 Amp 20 Pack Duplex GFCI						
2094-I20	20 125	Ivory	5-20R	•	•	
2094-W20	20 125	White	5-20R	•	•	



NEMA
5-15R



NEMA
5-20R

GFCIs with SafeLock™ Protection

New GFCIs with SafeLock Protection

If critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.

Available in trilingual (English, French, and Spanish) individual packages.



Trip indicator light makes it easy to identify tripped condition.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Prevents line-load reversal miswire: If miswired, GFCI can not be RESET.

Side or internal screw-pressure-plate back wire termination takes #14 - #10 AWG stranded or solid, copper or copper-clad conductors.


Grooved channel to ground screw allows for fast installation of ground wires.

Extra-long strap for better sheet rock contact eliminates "floaters" yet takes standard wall plate.

Two back wire holes per termination add wiring flexibility, eliminate pigtail, and save box space.

Line and load terminals backed out, ready-to-wire.

Improved resistance to surge, corrosion and electrical power line noise.



1594-LA

3RD PARTY COMPLIANCE

Catalog Number	Rating		Color	NEMA Config. No.	 UL943	 UL498	FSUL
	A.	VAC			C22.2 No. 144	C22.2 No. 42	
TradeMaster®/Spec Grade 15 Amp Duplex GFCI							
1594-I	15	125	Ivory*	5-15R	•	•	•
1594-W	15	125	White*	5-15R	•	•	•
1594	15	125	Brown	5-15R	•	•	•
1594-GRY	15	125	Gray*	5-15R	•	•	•
1594-BK	15	125	Black	5-15R	•	•	•
1594-LA	15	125	Light Almond*	5-15R	•	•	•

Specification Grade 20 Amp Duplex GFCI

2094-I	20 125	Ivory*	5-20R	•	•	
2094-W	20 125	White*	5-20R	•	•	
2094	20 125	Brown	5-20R	•	•	
2094-GRY	20 125	Gray	5-20R	•	•	
2094-BK	20 125	Black	5-20R	•	•	
2094-LA	20 125	Light Almond	5-20R	•	•	

Hospital Grade 15 Amp Duplex GFCI


1594-HGI	15 125	Ivory	5-15R	•	•	•
1594-HGW	15 125	White	5-15R	•	•	•
1594-HG	15 125	Brown	5-15R	•	•	•
1594-HGGRY	15 125	Gray	5-15R	•	•	•
1594-HGRED	15 125	Red	5-15R	•	•	•
1594-HGLA	15 125	Light Almond	5-15R	•	•	•

Hospital Grade 20 Amp Duplex GFCI

2094-HGI	20 125	Ivory	5-20R	•	•	
2094-HGW	20 125	White	5-20R	•	•	
2094-HG	20 125	Brown	5-20R	•	•	
2094-HGGRY	20 125	Gray	5-20R	•	•	
2094-HGRED	20 125	Red	5-20R	•	•	
2094-HGLA	20 125	Light Almond	5-20R	•	•	

3RD PARTY COMPLIANCE

Catalog Number	Rating		Color	 US	 US
	A.	VAC		UL943	UL508
				C22.2 No. 144	C22.2 No. 14
Specification Grade Dead Front GFCI - 1 1/2 HP Rating					
2084-IN	20	125	Ivory	•	•
2084-WN	20	125	White	•	•
2084-BKN	20	125	Black	•	•
2084-LAN	20	125	Light Almond	•	•



* Also available in 20 Packs. Add "20" to end of Catalog Number.

For additional technical or application-specific information - call 800-223-4185 or visit our Web site at www.passandseymour.com. We're eager to put our expertise to work for you.

Distributed by:

Pass & Seymour
legrand®
 The one that works for you.®

www.passandseymour.com

BR1129 10/02

Technical Specifications

TradeMaster® & Specification Grade

GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour
legrand®


Typical Specifications

Manufacturer's Identification: Pass & Seymour/Legrand 1594
Description: Straight Blade Duplex GFCI Receptacle
Type: 2 Pole, 3 Wire Grounding
Rating: 20A, 125VAC Feed Thru, 15A, 125VAC or 20A, 125VAC FACE
3rd Party Compliance: cULus Listed, File Number E42190; Standard UL498, Attachment Plugs and Receptacles UL943 GFCIs. Federal Specification WC596 (15A). Standard CSA-C22.2 No. 42, General-Use Receptacles, CSA-C22.2 No. 144 GFCIs. Conforms to NEMA WD-1, WD-6.



NEW

Catalog Number	Color	Rating	NEMA Configuration No.
☐ 1594-I	Ivory	15A 125VAC	5-15R
☐ 1594-W	White	15A 125VAC	5-15R
☐ 1594	Brown	15A 125VAC	5-15R
☐ 1594-GRY	Gray	15A 125VAC	5-15R
☐ 1594-RED	Red	15A 125VAC	5-15R
☐ 1594-LA	Light Almond	15A 125VAC	5-15R
☐ 1594-I20	Ivory	15A 125VAC	5-15R
☐ 1594-W20	White	15A 125VAC	5-15R
☐ 1594-LA20	Light Almond	15A 125VAC	5-15R
☐ 2094-I	Ivory	20A 125VAC	5-20R
☐ 2094-W	White	20A 125VAC	5-20R
☐ 2094	Brown	20A 125VAC	5-20R
☐ 2094-GRY	Gray	20A 125VAC	5-20R
☐ 2094-RED	Red	20A 125VAC	5-20R
☐ 2094-LA	Light Almond	20A 125VAC	5-20R
☐ 2094-I20	Ivory	20A 125VAC	5-20R
☐ 2094-LA20	Light Almond	20A 125VAC	5-20R



1594 Series



Performance

Electrical

Dielectric	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Voltage	125VAC
Voltage Range	102-132VAC
Operating Temp.	-35°C to +66°C
Maximum Humidity	95%

Mechanical

Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	#14 – #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are a permanent part of device

Environmental

Flammability	UL94 V2
--------------	---------


Materials

Face	Nylon	Terminal Screws	Steel # 8 – 32
Body	Nylon	Hex Head Grounding Screw	Steel (Green)
Contacts	.03" Brass (.8)	Flat Hd. Mtg. Screws	Steel-Zinc-Plated
Mounting Straps	.05" Zinc-Plated Steel (1.3)	Test/Reset Buttons	Nylon


Decorator Devices

TradeMaster® & Specification Grade
GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1594-I



2094-I

Features

- Meets new 2003 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: If miswired, GFCI cannot be RESET.
- Trip Indicator Light (red lamp).
- Improved resistance to surge, corrosion and electrical power line noise.
- Side or internal screw-pressure-plate back wire with #14 – #10 AWG solid or stranded copper wire.
- Line and load terminations supplied backed out and ready-to-wire.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Two back wire holes per terminal.
- Ultrasonic welding of face to back body.
- Button colors match the device face.
- Ground screw with a wire guide channel.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching nylon wall plate.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

	Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
					 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
NEW	TradeMaster/Spec Grade 15 Amp Duplex GFCI						
	1594-I	15 125	Ivory	5-15R	•	•	•
	1594-W	15 125	White	5-15R	•	•	•
	1594	15 125	Brown	5-15R	•	•	•
	1594-GRY	15 125	Gray	5-15R	•	•	•
	1594-BK	15 125	Black	5-15R	•	•	•
	1594-LA	15 125	Light Almond	5-15R	•	•	•
NEW	TradeMaster/Spec Grade 15 Amp 20 Pack Duplex GFCI						
	1594-I20	15 125	Ivory	5-15R	•	•	•
	1594-W20	15 125	White	5-15R	•	•	•
	1594-GRY20	15 125	Gray	5-15R	•	•	•
	1594-LA20	15 125	Light Almond	5-15R	•	•	•
NEW	Specification Grade 20 Amp Duplex GFCI						
	2094-I	20 125	Ivory	5-20R	•	•	
	2094-W	20 125	White	5-20R	•	•	
	2094	20 125	Brown	5-20R	•	•	
	2094-GRY	20 125	Gray	5-20R	•	•	
	2094-BK	20 125	Black	5-20R	•	•	
	2094-LA	20 125	Light Almond	5-20R	•	•	
NEW	Specification Grade 20 Amp 20 Pack Duplex GFCI						
	2094-I20	20 125	Ivory	5-20R	•	•	
	2094-W20	20 125	White	5-20R	•	•	

NEMA
5-15RNEMA
5-20R

Technical Specifications

TradeMaster® & Specification Grade

GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour
legrand®


Typical Specifications

Manufacturer's Identification: Pass & Seymour/Legrand 1594
Description: Straight Blade Duplex GFCI Receptacle
Type: 2 Pole, 3 Wire Grounding
Rating: 20A, 125VAC Feed Thru, 15A, 125VAC or 20A, 125VAC FACE
3rd Party Compliance: cULus Listed, File Number E42190; Standard UL498, Attachment Plugs and Receptacles UL943 GFCIs. Federal Specification WC596 (15A). Standard CSA-C22.2 No. 42, General-Use Receptacles, CSA-C22.2 No. 144 GFCIs. Conforms to NEMA WD-1, WD-6.



NEW

Catalog Number	Color	Rating	NEMA Configuration No.
☐ 1594-I	Ivory	15A 125VAC	5-15R
☐ 1594-W	White	15A 125VAC	5-15R
☐ 1594	Brown	15A 125VAC	5-15R
☐ 1594-GRY	Gray	15A 125VAC	5-15R
☐ 1594-RED	Red	15A 125VAC	5-15R
☐ 1594-LA	Light Almond	15A 125VAC	5-15R
☐ 1594-I20	Ivory	15A 125VAC	5-15R
☐ 1594-W20	White	15A 125VAC	5-15R
☐ 1594-LA20	Light Almond	15A 125VAC	5-15R
☐ 2094-I	Ivory	20A 125VAC	5-20R
☐ 2094-W	White	20A 125VAC	5-20R
☐ 2094	Brown	20A 125VAC	5-20R
☐ 2094-GRY	Gray	20A 125VAC	5-20R
☐ 2094-RED	Red	20A 125VAC	5-20R
☐ 2094-LA	Light Almond	20A 125VAC	5-20R
☐ 2094-I20	Ivory	20A 125VAC	5-20R
☐ 2094-LA20	Light Almond	20A 125VAC	5-20R



1594 Series



Performance

Electrical

Dielectric	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Voltage	125VAC
Voltage Range	102-132VAC
Operating Temp.	-35°C to +66°C
Maximum Humidity	95%

Mechanical

Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	#14 – #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are a permanent part of device

Environmental

Flammability	UL94 V2
--------------	---------

Materials

Face	Nylon	Terminal Screws	Steel # 8 – 32
Body	Nylon	Hex Head Grounding Screw	Steel (Green)
Contacts	.03" Brass (.8)	Flat Hd. Mtg. Screws	Steel-Zinc-Plated
Mounting Straps	.05" Zinc-Plated Steel (1.3)	Test/Reset Buttons	Nylon