



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## VDV427807 Punchdown Multi-Tool W/ 110/66 Blade & Workends

*Klein Tools*

Catalog Number	VDV427807
Manufacturer	Klein Tools
Description	Punchdown Multi-Tool, Punchdown Multi Tool With 110/66 Blade Type; Punchdown, Cut Operation Type; 110 Punchdown Block Connector Type; Color Code Yellow; Overall Length 7.88 Inch
Weight per unit	0.6000 (lbs/each)
Product Category	Punchdown Tools

### Features

Connector Type	110 PUNCH DOWN BLOCK
Operation Type	PUNCHDOWN, CUT

### Descriptions

Additional Information	COLOR CODED YELLOW ON THE CUT SIDE OF THE TOOL, INDUCTION HARDENED HIGH-CARBON STEEL FOR DURABILITY AND LONG LIFE, OVERALL LENGTH 7.88 INCH
Commodity Description	PUNCHDOWN TOOLS
Description	PUNCHDOWN MULTI-TOOL W/ 110/66 BLADE & WORKENDS
Long Description	PUNCHDOWN MULTI-TOOL, PUNCHDOWN MULTI TOOL WITH 110/66 BLADE TYPE; PUNCHDOWN, CUT OPERATION TYPE; 110 PUNCHDOWN BLOCK CONNECTOR TYPE; COLOR CODE YELLOW; OVERALL LENGTH 7.88 INCH
Product Type	Punchdown Multi-Tool

### Manufacturer Information

Brand	WorkEnds[T]
Manufacturers Part Number	VDV427-807
Model	VDV427

### Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	PUNCH DOWN MULTI TOOL WITH 66/110 BLADE

### Packaging

Carton	1
Package	2
Weight Per each	0.6

# Voice/Data/Video Tools

## Punchdown Multi-Tool

- Patent pending locking impact mechanism allows non-impact operation and sure driving with a variety of optional WorkEnds™ driver bits.
- Terminate and cut wire in one step with included precision ground combination 66 & 110 blade.
- Integrated Hook and Spudger for fast, easy manipulation of wire and small components.
- Selectable (Hi/Low) impact-force settings meet industry standards.
- Spring loaded for fast, low effort seating and terminating.
- Dual material contoured chassis provides greater control and enhances comfort.
- Blade storage compartment with spring loaded locking mechanism.
- Color coded yellow on the cut side of the tool.
- Hook and Spudger neatly and compactly store in the chassis, out of the way when not in use.
- Induction hardened high-carbon steel for durability and long life.
- Cat. No. VDV427-807 Includes WorkEnds™ Kit with WorkEnds™ adapter, reach extension, and 4 driver bits (#1 and #2 Phillips and 3/16" and 1/4" Slotted) in a convenient carrier.
- Replacement blades/accessories available: 110-Blade (VDV427-015), 66-Blade (VDV427-016), 66/110 Combination Blade (VDV427-017), Reach Extension (VDV427-018), WorkEnds™ Kit (VDV770-050).




VDV427-806



VDV427-807



Integrated Hook and Spudger for fast, easy manipulation of wire and small components.



Twisted Pair Cable



Cat. No	Set Contains	Overall Length	Weight (oz.)	
VDV427-806	punchdown multi-tool with 110/66 blade	7.0" (176 mm)	5.6	
Cat. No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2
VDV427-047	yellow/red/black	punchdown multi-tool chassis	-	-
VDV427-017	black	punchdown tool blade - combination 66/110 cut type	110 terminate & cut	66 terminate & cut
VDV427-807	punchdown multi-tool with 110/66 blade & WorkEnds™	7.88" (200 mm)	7.5	
Cat. No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2
VDV427-047	yellow/red/black	punchdown multi-tool chassis	-	-
VDV427-017	black	punchdown tool blade - combination 66/110 cut type	110 terminate & cut	66 terminate & cut
VDV770-050	-	WorkEnds™ kit	-	-

All dimensions are in inches and (millimeters).

**⚠WARNING:** Read carefully and understand instructions before using this tool.

**⚠WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** Never use on or near live electrical circuits.

