

Specifications



Eaton VS306U-W

Eaton vacancy sensor switch, No neutral connection, Flush, 120V, Wire leads, Maintained closure, White, Incand, MLV, ELV, Flrsnt, CFL, LED, halo, 1-pole, 3-way, 1-phase, 450 sq ft, Vacancy, 600W 722165

General specifications

PRODUCT NAME	Eaton vacancy sensor switch
CATALOG NUMBER	VS306U-W
UPC	032664722165
PRODUCT LENGTH/DEPTH	2.8 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Vacancy sensor switch

Product specifications

SPECIAL FEATURES	No neutral connection
TYPE	Vacancy sensor switch
VOLTAGE RATING	120 V
NUMBER OF POLES	Single-pole
PHASE	Single-phase
POWER CONSUMPTION	600 W
WIRING METHOD	Wire leads
SENSOR TYPE	Vacancy
MOUNTING METHOD	Flush
CLOSURE TYPE	Maintained
LOAD TYPE	HAL ELV LED INC FLR MLV CFL
NUMBER OF WAYS	Three-way
RANGE	450 sq ft
COLOR	White

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - VS306U-W](#)

[Eaton Passive infrared \(PIR\) motion spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

