Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WACDLASPL Accessory Dimmer, Light Almond

Eaton Wiring Devices

Catalog Number	WACDLASPL
Manufacturer	Eaton Wiring Devices
Description	Eaton Wi-Fi Smart Dimmer, Flush, 120V, Back and Side Wire, Light Almond, Single-Pole, Three-Way, 32°F to 104°F (0°C to 40°C), Single-Phase, Multi-Location, PC/PBT, WFD30, Wifi
Weight per unit	0.3700 (lbs/each)
Product Category	Wiring Devices

Features

dimensions	2.2600 IN X 2.2600 IN X 6.4100 IN
Phase	Single-phase
Voltage Rating	120 V

Descriptions

Description	ACCESSORY DIMMER, LIGHT ALMOND
extra long description	EWD WACD-LA-SP-L Accessory Dimmer,
Features	Wi-fi smart switches, receptacles, and dimmers from Eaton set up quickly and easily with Amazon's Alexa app–no other hubs or controllers are necessary. Plus Frustration Free Setup starts the connection automatically. Schedule lights to go on and off–and even dim–to fit your daily routine. Save energy and feel more comfortable and secure. You can even add voice-control using an Amazon Echo device.
Long Description	Eaton Wi-Fi smart dimmer, Flush, 120V, Back and side wire, Light Almond, Single-pole, Three-way, 32°F to 104°F (0°C to 40°C), Single-phase, Multi-location, PC/PBT, WFD30, WiFi
Product Type	Accessory Dimmer, Light Almond

Manufacturer Information

Brand	Eaton
GTIN	00786689366728
Manufacturers Part Number	WACD-LA-SP-L
UPC	786689366728

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Accessory

Availability

Status	Inactive

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	36
Weight Per each	0.37

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Operating Temperature	32 to 104 °F (0 to 40 °C)
standard	cULus Listed,NOM,cULus Listed