



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188



WLR1 Alum SGL RCPT CVR *Crouse-Hinds*

Catalog Number	WLR1
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series WLR1 Wet Location Cover, Copper-Free Aluminum, Vertical, 1-3/8", Gasket, Single Spring Door Cover, For Nema Configuration Round Receptacles
Weight per unit	0.3200 (lbs/each)
Product Category	Wall Plates & Covers

Features

dimensions	2.9100 IN X 1.1300 IN X 4.4400 IN
Material	Copper-Free Aluminum
Shape	Rectangle

Material, Color, and Finish

Finish	Epoxy
--------	-------

Dimensions and Weight

Size	2.91 In Length X 1.13 In Width X 4.44 In Height
------	---

Descriptions

Description	ALUM SGL RCPT CVR
extra long description	CRS-H WLR1 WET SGL SPDR CVR W/GASK
Features	WLR1, WLRD and WLG1 wet location covers from Eaton's Crouse-Hinds Division are suitable for use as general purpose utility receptacle covers, wherever portable equipment is required, in areas where electrical requirements do not exceed medium duty ratings. They are also used to mount FS and FD single-gang or multi-gang boxes having individual cover openings.
Long Description	Eaton Crouse-Hinds series WLR1 wet location cover, Copper-free aluminum, Vertical, 1-3/8", Gasket, Single spring door cover, for NEMA configuration round receptacles
Product Type	Wet SGL SPDR CVR W/Gask Dia. 1 3/8
Special Features	Gasket

Manufacturer Information

Brand	Eaton
GTIN	00782274128030
Manufacturers Part Number	WLR1
UPC	782274128030

Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	Wet location cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188

Packaging

Carton	1
Package	5
Weight Per each	0.32

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting	VERTICAL
standard	ANSI/UL 514A