



KT-WPLED60-M2-8XX-VDIM

ARCHITECTURAL FULL-CUTOFF LED WALL PACK

DESCRIPTION

Architectural 60W Full-Cutoff LED Wall Pack | 120–277V Input | 4000–5000K | Medium Housing | Bronze Finish | Wide Optic Lens

APPLICATION

Building mount for exterior illumination (perimeters, pathways, loading docks, and other general security lighting requirements)











PRODUCT FEATURES

- · Architectural full cutoff design that improves building appearance and optimizes functional light distribution
- Heavy duty die cast aluminum housing with (5) 1/2" threaded conduit hubs: (1) on back and (1) on all four sides
- Powered by Keystone 0–10V dimming LED drivers
- Dark Sky friendly performance that eliminates undesirable sky glow and glare
- Features one translucent 3/4" threaded plug with anti-yellowing agent for use with photocell accessory KT-WPLED-PS-UV-KO, sold separately
- Precision-crafted optical lens that provides wide distribution pattern ideal for increased fixture spacing and uniformity
- Covers footprint of mid-size HID wallpacks
- Ambient operating temperature: -40°C/-40°F to 50°C/122°F
- UL Certified for wet locations; IP65 rated
- Fixture impact rating IK08
- Power Factor: >0.95
- THD: <20%
- LED chip lifetime: L70 >100,000 hrs @ 25°C/77°F ambient fixture temperature
- Meets FCC Part 15, Part B, Class A standards for conducted and radiated emissions
- Compatible with Keystone LED Emergency Backups. See Accessories page for more details


PRODUCT SPECIFICATIONS

Catalog Number	Wattage	Lumens	Lumens Below 90º	Dimming	ССТ	Efficacy	CRI	Housing Color	Input Voltage	Rated Life	Legacy Equivalent
KT-WPLED60-M2-840-VDIM	60W	7500	7445	0-10V	4000K	125 lm/W	. 00	Dronzo	100 0771/	50.000 hrs	250W MH
KT-WPLED60-M2-850-VDIM		7800	7745	U-10V	5000K	130 lm/W	>80	Bronze	120–277V	50,000 nrs	






PHOTOMETRIC SPECIFICATIONS



LUMINOUS INTENSITY DISTRIBUTION



Average diffuse angle (50%): 114.29


- $1~Blue-0^{\varrho}~H$
- 2 Red 90º H
- 3 Green 22.5º H
- 4 Orange 45º H
- 5 Grey 67.5º H

FLUX DISTRIBUTION

Zone	Lumens	% Luminaire
Forward Light	4,722 lm	65.0%
0º-30º	907 lm	12.5%
30º-60º	2,329 lm	32.0%
60º-80º	1,327 lm	18.3%
80º-90º	159 lm	2.2%
Back Light	2,520 lm	34.6%
0º-30º	772 lm	10.6%
30º-60º	1,249 lm	17.2%
60º-80º	454 lm	6.2%
80º-90º	45 lm	0.6%
Up Light	25 lm	0.4%
90º-100º	4 lm	0.1%
1009-1809	21 lm	0.3%


MOUNTING

Side view



LIGHT DISTRIBUTION PATTERN


Isometric view from above; Luminaire mounted at 15'







PHYSICAL SPECIFICATIONS



GENERAL SETUP INSTRUCTIONS

GENERAL WIRING DIAGRAM



Caution: Before installing, make certain that AC power to the fixture is off.

Caution: The electrical rating of this product is 120-277V. Installer must confirm that there is 120-277V at the fixture before installation.





ACCESSORIES

SENSORS

Factory-Installable OR Field-Installable (field-installable purchased separately)

√ S	SUFFIX*	CATALOG NUMBER	DESCRIPTION	UPC	EASY CODE
	/MW3	KTS-MW3-UV-KO-K1	Microwave Sensor Kit, Includes 120-277V input to 12V DC convertor & 12V input sensor head, IP65. Bi-Level Control with Adjustable Hold Time, Dim Level and Standby Time. Installs via standard 1/2in KO	843654134147	BKG-51
	/PS	KT-WPLED-PS-UV-KO	Dawn to Dusk Photocell for WallPack fixtures. Fits M1, M2, L1 housings. 120-277V Input. Install via standard 1/2in KO	843654129198	DLU-58



^{*} For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).

CORD SETS

Factory-Installable OR Field-Installable (field-installable purchased separately)

\checkmark	SUFFIX*	CATALOG NUMBER	DESCRIPTION	UPC	EASY CODE
	/515P6	KT-CS-515P-6-18/3	Cord set for high bay; 125V NEMA 5-15P; straight blade plug; 6' SJTOW cable; 18/3 wire	843654140124	UKH-26
	/L515P6	KT-CS-L515P-6-16/3	Cord set for high bays; 250V NEMA L5-15P; twist lock plug; 6' SJTOW cable; 16/3 wire	843654140186	POC-82



Cord Sets

(Accessories continued on next page)

^{*} For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet). **Note:** For cord sets not listed here, please contact your Keystone sales rep.






ACCESSORIES (continued)

EMERGENCY BACKUP

Factory-Installable OR Field-Installable (field-installable purchased separately)

\checkmark	SUFFIX*	CATALOG NUMBER	DESCRIPTION	UPC	EASY CODE
	/EM12	KT-EMRG-LED-12C-1200	LED Emergency Back-Up, 12W Constant Wattage Design. Approx 1200 Lumens. 120-277V Input. Remote Compact Battery Pack. CEC T20 Compliant.	843654103112	OJQ-32
	-	KT-EMRG-LED2-TS-IP65	IP65 Rated Wet Location Test Switch for 5W and 12W CEC Compliant LED Emergency Packs	843654130019	MDB-29





^{*} For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).
† Factory installation of emergency backup units will automatically include any relevant mounting bracket.

MOUNTS AND BRACKETS

Field-Installable / Field-Use ONLY (purchased separately)

\checkmark	SUFFIX*	CATALOG NUMBER	DESCRIPTION	UPC	EASY CODE
	-	KT-WPLED-BP-M	Back Plate for Medium Size Wallpacks, Covers Legacy Style Large HID Housing Dimensions. Standard Bronze Color.	843654130613	CCJ-21
		P-M * For factory installation of a	accessory, add suffix to fixture part number (see ordering examples and instructions on last page of s M - will be added when factory installing EM	pec sheet).	

SURGE PROTECTORS

Factory-Installable OR Field-Installable (field-installable purchased separately)

\checkmark	SUFFIX*	CATALOG NUMBER	DESCRIPTION	UPC	EASY CODE
	/10KV	KTSP-10KV-C	External Surge Protector, compact design. Parallel Wiring, 120-277V Input, Max Peak Protection (10KV, 10KA)	843654129204	BUU-26



^{*} For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).





KT-WPLED60-M2-8XX-VDIM

ARCHITECTURAL FULL-CUTOFF LED WALL PACK

ORDERING INFORMATION

CATALOG NUMBER	PACK QTY.	UPC	EASY CODE	DLC PRODUCT ID
KT-WPLED60-M2-840-VDIM	1	843654129075	VMR-18	PIKA3HFT
KT-WPLED60-M2-850-VDIM	1	843654129082	OYW-93	PPT7NCOK

CATALOG NUMBER BREAKDOWN

KT-WPLED60-M2-8XX-VDIM

Wallpack

4000K

5000K

WP

8 CCT

40

50

1 Keystone Technologies

- 2 Fixture Type
- 3 LED Lamp
- 4 Max Wattage
- 5 Size
- 6 Style
- 7 CRI
- 8 CCT
- 9 Dimming
- 10 Additional Options

4 5 6 7 8 9 2 Fixture Type 5 Size 6 S

VDIM

5 Size

M Medium

9 Dimming

0-10V

6 Style
2 Full-Cutoff

10

7 CRI 8

>80

ORDERING EXAMPLES

FIXTURE WITH MULTIPLE FACTORY-INSTALLED ACCESSORIES*


KT-WPLED60-M2-8XX-VDIM /MW3/515P6/EM12

FIXTURE WITH SINGLE FACTORY-INSTALLED ACCESSORY KT-WPLED60-M2-8XX-VDIM /MW3

FIXTURE WITH NO FACTORY-INSTALLED ACCESSORIES

KT-WPLED60-M2-8XX-VDIM

KEYSTONE FIXTURE CATALOG NUMBER KT-WPLED60-M2-8XX-VDIM SENSORS ✓ SUFFIX CATALOG NUMBER ✓ /MW3 KTS-MW3-UV-KO-K1 CORD SETS ✓ SUFFIX CATALOG NUMBER ✓ /515P6 KT-CS-515P-6-18/3



^{*} When ordering more than one factory-installed accessory, use multiple suffixes as shown in the ordering examples above.

Note: All accessories can also be ordered separately for field installation using just their regular Catalog Number, UPC, or Easy Code.