


Specifications



Photo is representative



Eaton WR5462W

Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 20A, Flush, 250V, Back and Side, White, Brass, Weather resistant, High-impact nylon face, Glass-filled nylon base, 6-20R, Duplex, Screw, Nylon, Core pack

General specifications

PRODUCT NAME	Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle
CATALOG NUMBER	WR5462W
UPC	032664759062
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.19 lb
CERTIFICATIONS	UL 498 cULus Listed
PRODUCT TYPE	Extra heavy-duty industrial specification grade

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	250V
CONTACT MATERIAL	Brass
FEATURES	Weather resistant Auto-grounding
APPLICATION	Industrial
DEVICE GRADE	Extra heavy-duty industrial specification grade
WIRING METHOD	Back and side
ENVIRONMENTAL CONDITIONS	Damp/wet
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
MATERIAL	Nylon
PACKAGING TYPE	Core pack
ENVIRONMENTAL RESISTANCE	Weather resistant
COLOR	White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	6-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Glass-filled nylon base High-impact nylon face
RECEPTACLE TYPE	Duplex

Resources

BROCHURES	Spec grade receptacles brochure
MULTIMEDIA	Residential straight blade receptacles Eaton Specification Sheet - WR5462W
SPECIFICATIONS AND DATASHEETS	Arrow Hart heavy-duty straight blade duplex receptacles

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.


Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton WR5462W

Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 20A, Flush, 250V, Back and Side, White, Brass, Weather resistant, High-impact nylon face, Glass-filled nylon base, 6-20R, Duplex, Screw, Nylon, Core pack

General specifications

PRODUCT NAME	Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle
CATALOG NUMBER	WR5462W
UPC	032664759062
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.19 lb
CERTIFICATIONS	UL 498 cULus Listed
PRODUCT TYPE	Extra heavy-duty industrial specification grade

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	20A
VOLTAGE RATING	250V
CONTACT MATERIAL	Brass
FEATURES	Weather resistant Auto-grounding
APPLICATION	Industrial
DEVICE GRADE	Extra heavy-duty industrial specification grade
WIRING METHOD	Back and side
ENVIRONMENTAL CONDITIONS	Damp/wet
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
MATERIAL	Nylon
PACKAGING TYPE	Core pack
ENVIRONMENTAL RESISTANCE	Weather resistant
COLOR	White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	6-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Glass-filled nylon base High-impact nylon face
RECEPTACLE TYPE	Duplex

Resources

BROCHURES	Spec grade receptacles brochure
MULTIMEDIA	Residential straight blade receptacles
	Eaton Specification Sheet - WR5462W
SPECIFICATIONS AND DATASHEETS	Arrow Hart heavy-duty straight blade duplex receptacles

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

