



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WWCRC Red Wing Wire Connector 100/BK

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | WWCRC  |
| Manufacturer     | Nsi Industries   |
| Description      | Winged Wire Connector, (3) #16 Awg Conductor Size, (5) #12 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Red Insulation Color, +221 °F Operating Temperature, 0.906 In Overall Width, 1.252 In Overall Height, 600 V, 0.79 LB |
| Weight per unit  | 0.7900 (lbs/each)  |
| Product Category | Electrical Fixture Conn ( Nuts   |

### Features

|                      |              |
|----------------------|--------------|
| Number of Conductors | 1            |
| Voltage Rating       | 600 V        |
| Warranty             | 1 YEAR       |
| Wire Type            | CU Wire Only |

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Finish | Thermoplastic |
|--------|---------------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | RED WING WIRE CONNECTOR 100/BK      |
| extra long description | NSI WWC-R-C WW Glass Cloth Tape .75 |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00662381361745 |
| UPC  | 662381361745   |

### Taxonomies, Classifications, and Categories

|                      |           |
|----------------------|-----------|
| Category Description | WIRE NUTS |
|----------------------|-----------|

### Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 100  |
| Weight Per each | 0.79 |

### Uses, Certifications, and Standards

|                          |       |
|--------------------------|-------|
| environmental conditions | 105 C |
| Temperature Rating       | 105 C |