



Powering Business Worldwide

pe.eaton.com

8.2 mm Screw connection single level-through-feed

XBUT6

UPC:782116904945

Dimensions:

- **Height:** X
- **Length:** .323 IN
- **Width:** X

Warranties:

- 1 year

Specifications:


- **Type:** IEC-XB Series
- **Amperage Rating:** 527 (IEC), 40A (EN), 50A (EN), 50A (UL)
- **Voltage Rating:** IEC 800V, EN 700V, UL 600V
- **Maximum Wire Size:** 8 AWG/6 mm²
- **Wire Size:** #24-8 AWG
- **Color:** Gray

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XBUT6 AutoCAD 2D Footprint](#)
- [XBUT6 AutoCAD 2D Footprint \(mm\)](#)
- [XBUT6 3D Model Xchange](#)
- [XBUT6 3D Inventor](#)
- [XBUT6 2D PDF](#)
- [XBUT6 2D Drawing Xchange](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT6](#)

Certifications:

- UL Listed
- CSA Certified



Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

8.2 mm Screw connection single level-through-feed

XBUT6

UPC:782116904945

Dimensions:

- **Height:** X
- **Length:** .323 IN
- **Width:** X

Warranties:

- 1 year

Specifications:


- **Type:** IEC-XB Series
- **Amperage Rating:** 527 (IEC), 40A (EN), 50A (EN), 50A (UL)
- **Voltage Rating:** IEC 800V, EN 700V, UL 600V
- **Maximum Wire Size:** 8 AWG/6 mm²
- **Wire Size:** #24-8 AWG
- **Color:** Gray

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XBUT6 AutoCAD 2D Footprint](#)
- [XBUT6 AutoCAD 2D Footprint \(mm\)](#)
- [XBUT6 3D Model Xchange](#)
- [XBUT6 3D Inventor](#)
- [XBUT6 2D PDF](#)
- [XBUT6 2D Drawing Xchange](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT6](#)

Certifications:

- UL Listed
- CSA Certified



Product compliance: No Data

© 2016 Eaton. All rights reserved.