



COVER ASSEMBLIES • CONTROL STATIONS



Single Push Button (Box and Cover)



Double Push Button (Box and Cover)



Three Mini-Push Button (Box and Cover)



Push-Pull Mushroom Maintained Push Button (Box and Cover)

Class I, Div. 1 & 2, Groups C, D
 Class I, Zones 1 & 2, Groups IIB, IIA
 Class II, Div. 1 & 2, Groups E, F, G
 Class III
 NEMA 7 (C, D) 9 (E, F, G)

UL LISTED - File E53360

SP Certified - File LR11714

See files for details or call Killark.

FEATURES-SPECIFICATIONS

XCS MOMENTARY CONTACT SINGLE PUSH BUTTON						
COVER WITH DEVICE	CATALOG NUMBER		HUB SIZE	DIAGRAM	BUTTON COLOR ^②	NAMEPLATE MARKETING ^①
	COMPLETE UNITS (BOX & COVER)					
	DEAD-END	FEED-THRU				
XCS-0B1	XCS-1B1	XCS-4B1	1/2"		GREEN	START
	XCS-2B1	XCS-5B1	3/4"			
XCS-0B2	XCS-1B2	XCS-4B2	1/2"		RED	STOP
	XCS-2B2	XCS-5B2	3/4"			
XCS-0B3	XCS-1B3	XCS-4B3	1/2"		BLACK	SPECIFY
	XCS-2B3	XCS-5B3	3/4"			

XCS MOMENTARY CONTACT DOUBLE PUSH BUTTON						
COVER WITH DEVICE	CATALOG NUMBER		HUB SIZE	DIAGRAM	BUTTON COLOR ^②	NAMEPLATE MARKETING ^①
	COMPLETE UNITS (BOX & COVER)					
	DEAD-END	FEED-THRU				
XCS-0B4	XCS-1B4	XCS-4B4	1/2"		GREEN-RED	START/STOP
	XCS-2B4	XCS-5B4	3/4"			
XCS-0B4-U	XCS-1B4-U	XCS-4B4-U	1/2"		GREEN-RED	START/STOP
	XCS-2B4-U	XCS-5B4-U	3/4"			
XCS-0B5	XCS-1B5	XCS-4B5	1/2"		GREEN-GREEN	START/START
	XCS-2B5	XCS-5B5	3/4"			
XCS-0B7	XCS-1B7	XCS-4B7	1/2"		BLACK-BLACK	SPECIFY
	XCS-2B7	XCS-5B7	3/4"			

XCS MOMENTARY CONTACT THREE MINI-PUSH BUTTON						
COVER WITH DEVICE	CATALOG NUMBER		HUB SIZE	DIAGRAM	BUTTON COLOR ^②	NAMEPLATE MARKETING ^①
	COMPLETE UNITS (BOX & COVER)					
	DEAD-END	FEED-THRU				
XCS-0A8	XCS-1A8	XCS-4A8	1/2"		GREEN-RED	START/STOP
	XCS-2A8	XCS-5A8	3/4"			
XCS-0A9	XCS-1A9	XCS-4A9	1/2"		BLACK	SPECIFY
	XCS-2A9	XCS-5A9	3/4"			

① For other than standard marking, see page C59 and order separately or as modified products.

② Lens colors other than listed may be specified by changing lens color suffix. See modifications, page C50.

For control stations with 1" conduit openings or for multi-gang assemblies, order cover with devices and box as separate components.

XCS MAINTAINED CONTACT PUSH PULL MUSHROOM PUSH BUTTON ^④			
CATALOG NUMBER (COVER WITH DEVICE)	DIAGRAM	BUTTON COLOR	NAMEPLATE MARKETING
XCS-OMMG3		GREEN	③
XCS-OMMR3		RED	
XCS-OMMK3		BLACK	

③ Three nameplates supplied (Start/Stop, Blank, Emergency Stop) with XCS maintained push button.

④ Operation - when push button is depressed and contact activated, operator will remain in depressed position until pulled out in normal position.



COVER ASSEMBLIES • CONTROL STATIONS



Pilot Light
(Box and Cover)



Double
Pilot Light
(Box and Cover)



Pilot Light
Push Button
(Box and Cover)



Pilot Light
Two Mini Push Buttons
(Box and Cover)

Class I, Div. 1 & 2, Groups C, D
Class I, Zones 1 & 2, Groups IIB, IIA
Class II, Div. 1 & 2, Groups E, F, G
Class III
NEMA 7 (C, D) 9 (E, F, G)

UL LISTED - File E53360

SP Certified - File LR11714

See files for details or call Killark.

FEATURES-SPECIFICATIONS

XCS PILOT LIGHT ^③							
COVER WITH DEVICE	CATALOG NUMBER		HUB SIZE	DIAGRAM	LAMP VOLTS	LENS COLOR ^②	NAMEPLATE MARKING ^①
	COMPLETE UNITS (BOX & COVER)						
	DEAD-END	FEED-THRU					
XCS-0B24-CL	XCS-1B24-CL	XCS-4B24-CL	1/2"		120V	CLEAR	SPECIFY
	XCS-2B24-CL	XCS-5B24-CL	3/4"				
XCS-0B24-GL	XCS-1B24-GL	XCS-4B24-GL	1/2"		120V	GREEN	SPECIFY
	XCS-2B24-GL	XCS-5B24-GL	3/4"				
XCS-0B24-RL	XCS-1B24-RL	XCS-4B24-RL	1/2"		120V	RED	SPECIFY
	XCS-2B24-RL	XCS-5B24-RL	3/4"				

XCS DOUBLE PILOT LIGHT ^④							
COVER WITH DEVICE	CATALOG NUMBER		HUB SIZE	DIAGRAM	LAMP VOLTS	LENS COLOR ^②	NAMEPLATE MARKING ^①
	COMPLETE UNITS (BOX & COVER)						
	DEAD-END	FEED-THRU					
XCS-0B30-CL	XCS-1B30-CL	XCS-4B30-CL	1/2"		120V	CLEAR	SPECIFY
	XCS-2B30-CL	XCS-5B30-CL	3/4"				
XCS-0B30-GL	XCS-1B30-GL	XCS-4B30-GL	1/2"		120V	GREEN	SPECIFY
	XCS-2B30-GL	XCS-5B30-GL	3/4"				
XCS-0B30-RL	XCS-1B30-RL	XCS-4B30-RL	1/2"		120V	RED	SPECIFY
	XCS-2B30-RL	XCS-5B30-RL	3/4"				
XCS-0B30RL-GL	XCS-1B30RL-GL	XCS-4B30RL-GL	1/2"		120V	RED/GREEN	SPECIFY
	XCS-2B30RL-GL	XCS-5B30RL-GL	3/4"				

XCS MOMENTARY CONTACT PUSH BUTTON AND PILOT LIGHT ^④								
COVER WITH DEVICE	CATALOG NUMBER		HUB SIZE	DIAGRAM	BUTTON COLOR	LENS COLOR ^②	NAMEPLATE MARKING ^①	
	COMPLETE UNITS (BOX & COVER)						BUTTON	LENS
	DEAD-END	FEED-THRU						
XCS-0B13-C	XCS-1B13-C	XCS-4B13-C	1/2"		RED	RED	STOP	SPECIFY
	XCS-2B13-C	XCS-5B13-C	3/4"					
XCS-0B13-0	XCS-1B13-0	XCS-4B13-0	1/2"		GREEN	RED	START	SPECIFY
	XCS-2B13-0	XCS-5B13-0	3/4"					
XCS-0B13-U	XCS-1B13-U	XCS-4B13-U	1/2"		BLACK	RED	SPECIFY	SPECIFY
	XCS-2B13-U	XCS-5B13-U	3/4"					

XCS MOMENTARY CONTACT TWO MINI PUSH BUTTONS AND PILOT LIGHT ^④								
COVER WITH DEVICE	CATALOG NUMBER		HUB SIZE	DIAGRAM	BUTTON COLOR	LENS COLOR ^②	NAMEPLATE MARKING ^①	
	COMPLETE UNITS (BOX & COVER)						BUTTON	LENS
	DEAD-END	FEED-THRU						
XCS-0A15	XCS-1A15	XCS-4A15	1/2"		RED	RED	STOP	SPECIFY
	XCS-2A15	XCS-5A15	3/4"					

① For other than standard marking, see page C59 and order separately or as modified products.

② Lens color suffix listed in modifications, page C50. Unless different lens colors are specified by proper suffix catalog number, red lens will be provided.

③ Pilot light transformers also listed in modifications. Add suffix to cover assembly catalog number.

④ Pilot light transformers will not fit in these assemblies. When transformer is desired, use SWB-14, indicating conduit openings required from chart on page C52 of this section. See page C50 for required transformer suffix. One transformer required for each lamp. For control stations with 1" conduit openings or for multi-gang assemblies, order cover and box as separate components.



COVER ASSEMBLIES • CONTROL STATIONS



Selector Switch



Key Operated

Class I, Div. 1 & 2, Groups C, D
 Class I, Zones 1 & 2, Groups IIB, IIA
 Class II, Div. 1 & 2, Groups E, F, G
 Class III
 NEMA 7 (C, D) 9 (E, F, G)

UL LISTED - File E53360

SP Certified - File LR11714

See files for details or call Killark.

FEATURES-SPECIFICATIONS

XCS TWO POSITION SELECTOR SWITCH (MAINTAINED)*								
CATALOG NUMBER			HUB SIZE	TWO POSITION DIAGRAM				NAMEPLATE MARKING ^①
COVER WITH DEVICE	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		RIGHT POSITION		
	DEAD-END	FEED-THRU		LEFT BLOCKS	RIGHT BLOCKS	LEFT BLOCKS	RIGHT BLOCKS	
XCS-0S2A1	XCS-1S2A1	XCS-4S2A1	1/2"					OFF/ON
	XCS-2S2A1	XCS-5S2A1	3/4"					
XCS-0S2A5	XCS-42S2A5	XCS-45S2A5	3/4"					OFF/ON

XCS THREE POSITION SELECTOR SWITCH (MAINTAINED)*										
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM						NAMEPLATE MARKING
COVER WITH DEVICE	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION		
	DEAD-END	FEED-THRU		LEFT BLOCKS	RIGHT BLOCKS	LEFT BLOCKS	RIGHT BLOCKS	LEFT BLOCKS	RIGHT BLOCKS	
XCS-0S3C4	XCS-1S3C4	XCS-4S3C4	1/2"							HOA
	XCS-2S3C4	XCS-5S3C4	3/4"							
XCS-0S3C5	XCS-42S3C5	XCS-45S3C5	3/4"							HOA

^① For other than standard marking, see page C59 and order separately or as modified products.

For control stations with 1" conduit openings or for multi-gang assemblies, order cover with devices and box as separate components.

XCS TWO POSITION KEY OPERATED SELECTOR SWITCH (MAINTAINED)*								
CATALOG NUMBER			HUB SIZE	TWO POSITION DIAGRAM				NAMEPLATE MARKING ^①
COVER WITH DEVICE	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		RIGHT POSITION		
	DEAD-END	FEED-THRU		LEFT BLOCKS	RIGHT BLOCKS	LEFT BLOCKS	RIGHT BLOCKS	
XCS-0K2A1	XCS-1K2A1	XCS-4K2A1	1/2"					OFF/ON
	XCS-2K2A1	XCS-5K2A1	3/4"					
XCS-0K2A5	XCS-42K2A5	XCS-45K2A5	3/4"					OFF/ON

XCS THREE POSITION KEY OPERATED SELECTOR SWITCH (MAINTAINED)*										
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM						NAMEPLATE MARKING
COVER WITH DEVICE	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION		
	DEAD-END	FEED-THRU		LEFT BLOCKS	RIGHT BLOCKS	LEFT BLOCKS	RIGHT BLOCKS	LEFT BLOCKS	RIGHT BLOCKS	
XCS-0K3C4	XCS-1K3C4	XCS-4K3C4	1/2"							HOA
	XCS-2K3C4	XCS-5K3C4	3/4"							
XCS-0K3C5	XCS-42K3C5	XCS-45K3C5	3/4"							HOA

^① For other than standard marking, see page C59 and order separately or as modified products.

* Key removal in all positions for 2 & 3 position key operated selectors. Consult factory for variations.

For control stations with 1" conduit openings or for multi-gang assemblies, order cover with devices and box as separate components.

Keyed sub-assemblies are supplied with random keys. For like keys, add "A" to end of catalog number. i.e. XCS-0K3C4A



COVER ASSEMBLIES • CONTROL STATIONS



Selector Switch

Class I, Div. 1 & 2, Groups C, D
 Class I, Zones 1 & 2, Groups IIB, IIA
 Class II, Div. 1 & 2, Groups E, F, G
 Class III
 NEMA 7 (C, D) 9 (E, F, G)

LISTED - File E53360

Certified - File LR11714
 See files for details or call Killark.

FEATURES-SPECIFICATIONS

XCS SPRING RETURN SELECTOR SWITCH – TWO POSITION SPRING RETURN TO LEFT							
CATALOG NUMBER			HUB SIZE	TWO POSITION DIAGRAM – 1N.O./1N.C.			
COVER WITH DEVICE ^①	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0S2L3F	XCS-42S2L3F	XCS-45S2L3F	3/4"				

XCS SPRING RETURN SELECTOR SWITCH – THREE POSITION SPRING RETURN TO CENTER FROM RIGHT AND LEFT									
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM – 2 N.O.					
COVER WITH DEVICE ^①	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0S3M6G	XCS-42S3M6G	XCS-45S3M6G	3/4"						

XCS SPRING RETURN SELECTOR SWITCH – THREE POSITION SPRING RETURN TO CENTER FROM RIGHT, MAINTAIN IN LEFT									
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM – 2 N.O.					
COVER WITH DEVICE ^①	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0S3L6G	XCS-42S3L6G	XCS-45S3L6G	3/4"						

XCS SPRING RETURN SELECTOR SWITCH – THREE POSITION SPRING RETURN TO CENTER FROM LEFT, MAINTAIN IN RIGHT									
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM – 2 N.O.					
COVER WITH DEVICE ^①	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0S3R6G	XCS-42S3R6G	XCS-45S3R6G	3/4"						

^① All spring return assemblies must be installed on deep style box SWB-14 or SWB-18 through SWB-49.
 For control stations with 1" conduit openings or for multi-gang assemblies, order cover with devices and box as separate components.



CONTROLS

COVER ASSEMBLIES • CONTROL STATIONS



Key Operated

Class I, Div. 1 & 2, Groups C, D
 Class I, Zones 1 & 2, Groups IIB, IIA
 Class II, Div. 1 & 2, Groups E, F, G
 Class III
 NEMA 7 (C, D) 9 (E, F, G)

LISTED - File E53360

Certified - File LR11714
 See files for details or call Killark.

FEATURES-SPECIFICATIONS

XCS KEY OPERATED SPRING RETURN SELECTOR SWITCH ① – TWO POSITION SPRING RETURN TO LEFT									
CATALOG NUMBER			HUB SIZE	TWO POSITION DIAGRAM – 1 N.O./1 N.C.					
COVER WITH DEVICE ②	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		RIGHT POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0K2L3F22D	XCS-42K2L3F22D	XCS-45K2L3F22D	3/4"						

XCS KEY OPERATED SPRING RETURN SELECTOR SWITCH ① – THREE POSITION SPRING RETURN TO CENTER FROM RIGHT AND LEFT									
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM – 2 N.O.					
COVER WITH DEVICE ②	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0K3M6G32D	XCS-42K3M6G32D	XCS-45K3M6G32D	3/4"						

XCS KEY OPERATED SPRING RETURN SELECTOR SWITCH ① – THREE POSITION SPRING RETURN TO CENTER FROM RIGHT, MAINTAIN IN LEFT									
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM – 2 N.O.					
COVER WITH DEVICE ②	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0K3L6G32D	XCS-42K3L6G32D	XCS-45K3L6G32D	3/4"						

XCS KEY OPERATED SPRING RETURN SELECTOR SWITCH ① – THREE POSITION SPRING RETURN TO CENTER FROM LEFT, MAINTAIN IN RIGHT									
CATALOG NUMBER			HUB SIZE	THREE POSITION DIAGRAM – 2 N.O.					
COVER WITH DEVICE ②	COMPLETE UNITS (BOX & COVER)			LEFT POSITION		CENTER POSITION		RIGHT POSITION	
	DEAD-END	FEED-THRU		LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK	LEFT BLOCK	RIGHT BLOCK
XCS-0K3R6G32D	XCS-42K3R6G32D	XCS-45K3R6G32D	3/4"						

① All key operators are furnished keyed different. If keyed alike is required substitute letter "A" for "D" at end of catalog number. Keys are removable in left position for 2 position selectors and in center position for 3 position selectors. For key removable in all positions change "22" in 2 position to "20" and "32" in 3 position to "30".

② All spring return assemblies must be installed on deep style box SWB-14 or SWB-18 through SWB-49. For control stations with 1" conduit openings or for multi-gang assemblies, order cover with devices and box as separate components.



BLANK ACCESSORIES / REPLACEMENT PARTS



X-10
Blank Cover



KIT-69



KIT-78



KIT-64

X BLANK AND SPECIAL COVERS	
CAT. NO.	DESCRIPTION
X-10	Blank cover for SWB
X-60	Cover with (1) 3/4" NPSM Hole ^①
X-64	Cover with (2) 3/4" NPSM Holes ^{① ②}

^① For "G" series short operators.

^② When X-64 cover is used, one operator must be a pilot light due to electrical clearances.

XS REPLACEMENT SWITCH ONLY	
CAT. NO.	DESCRIPTION
KIT-264	Replacement switch for XS-1C
KIT-266	Replacement switch for XS-2C
KIT-263	Replacement switch for XS-6C
KIT-265	Replacement switch for XS-8C

REPLACEMENT XCS COVER INTERIORS SUPPLIED WITH MOUNTING HARDWARE	
KIT-62	INTERIOR DEVICE XCS-0A8
KIT-63	INTERIOR DEVICE XCS-0A9
KIT-64	INTERIOR DEVICE XCS-0A15
KIT-66	INTERIOR DEVICE XCS-0B1
KIT-67	INTERIOR DEVICE XCS-0B2
KIT-68	INTERIOR DEVICE XCS-0B3
KIT-69	INTERIOR DEVICE XCS-0B4
KIT-70	INTERIOR DEVICE XCS-0B5
KIT-72	INTERIOR DEVICE XCS-0B7
KIT-73	INTERIOR DEVICE XCS-0B13-C
KIT-74	INTERIOR DEVICE XCS-0B13-O
KIT-75	INTERIOR DEVICE XCS-0B13-U
KIT-76	INTERIOR DEVICE XCS-0B24*
KIT-78	INTERIOR DEVICE XCS-0B30*

Kits supplied with contacts and lamp sockets mounted to strap for installation on SWB back box. All lamps are incandescent 120V.



Standard Lockout




Miniature Lockout



Selector Lockout



Dust/Weather Cap



GOM Lockout

ACCESSORIES					
CATALOG NUMBER				DESCRIPTION	
PUSH BUTTON ^① LOCKOUT	SELECTOR LOCKOUT ^①	DUST/WEATHER CAP			
		RED	GREEN	BLACK	
XLOB	G0567-LOK	XDBR	XDBG	XDBB	Standard operator
XLOA	—	—	—	—	Miniature operator

^① Must be factory installed

CATALOG NUMBER GOMLOCK ^②
LOCKOUT FOR MAINTAINED PUSH BUTTON COVERS
XCS-OMMR3
FXCS-OMMR3, FXCS - *MMR3-M

^② May be installed in field.

XCS REPLACEMENT COVER SCREWS	
CATALOG NUMBER	DESCRIPTION
00891896	4 Cover Screws
00891898	4 Cover Screws and 2 Strap Screws