



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XJG54SA 1-1/2" Alu Expansion Joint

Crouse-Hinds

Catalog Number	XJG54SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series XJG Expansion Coupling, Rigid/Imc, Copper-Free Aluminum, 4" Maximum Conduit Movement, 1-1/2" Trade Size
Weight per unit	2.5 (lbs/each)
Product Category	Aluminum

Features

dimensions	8.0000 IN X 3.6200 IN X 3.6200 IN
Material	Copper Free Aluminum

Descriptions

Description	1-1/2" ALU EXPANSION JOINT
extra long description	CRS-H XJG54 SA 1 1/2 AL CND EXP JNT
Features	"XJG conduit expansion couplings for EMT and rigid/IMC are used with EMT, rigid metal conduit and IMC to couple together two sections of conduit subject to longitudinal movement. They are installed indoors or outdoors in long conduit runs to permit linear movement caused by thermal expansion and contraction to prevent damage to conduit supports and electrical systems in building or bridges. XJGs for rigid/IMC and EMT are also available with a hot dip galvanized finish (standard for trade sizes 1-1/4" and
Long Description	Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 1-1/2" trade size
Product Type	1 1/2 Al CND Exp JNT Int GRD Max MVT 4

Manufacturer Information

Brand	Eaton
GTIN	00782274915883
Manufacturers Part Number	XJG54 SA
UPC	782274915883

Taxonomies, Classifications, and Categories

Category Description	RIGID COUPLINGS
Type	Expansion coupling

Packaging

Carton	1
Weight Per each	2.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	NEMA FB1
standard	UL 514B, CSA C22.2