	ENCLOSURE												PANS AND HINGES						
	Mounting Lug Mtg.										Steel								
XCE/XJF Catalog #								CL to CL E F		Bolt Size	Ship Weight	Pan Catalog # Steel Alum. Phen		Nom. Dimensions W H		Pan Weight	Hinge Cat #		
123006	12	30	6	Depth 6 11/16	16 34	34 1/4	9 %	23	16	1/2	180		XSA1230		10 3/4	28 ¾	9 ¾	XHC-2	
123606	12	36	6	6 15/16	16 1/4	40 1/4	9 11/16	29	16	1/2	212		XSA1236		10 ¾	34 ¾	11 3/4	XHD-3	
123608	12	36	8	8 <sup>15</sup> / <sub>16</sub>	16 1/4	40 1/4	11 11/16	29	16	1/2	232		XSA1236		10 34	34 ¾	11 ¾	XHD-3	
124608	12	46	8	8 <sup>15</sup> / <sub>16</sub>	16 1/4	50 1/4	11 11/16	39	16	5/8	280		XSA1246		10 34	44 3/4	15	XHD-4	
141404	14	14	4	5	18 1/4	18 1/4	7 1/8	9 3/4	17 ¾	1/2	91		XSA1414		12 %	12 %	5	XHC-2	
141406	14	14	6	7	18 1/4	18 1/4	9 1/4	9 3/4	17 ¾	1/2	97		XSA1414		12 %	12 %	5	XHC-2	
141408	14	14	8	9	18 1/4	18 1/4	11 1/8	9 ¾	17 ¾	1/2	103	XSM1414	XSA1414	XSB1414	12 %	12 %	5	XHC-2	
142210**	14	22	10	11 1/4	18 1/4	26 1/4	13 %	16 ½	17 ¾	1/2	181		XSA1422		12 %	20 %	8	XHD-2	
142213**	14	22	10	13	18 1/4	26 1/4	15 1/8	16 ½	17 ¾	1/2	235	XSM1422	XSA1422	XSB1422	12 %	20 %	8	XHD-2	
142806	14	28	6	7 <sup>13</sup> /16	18 1/4	32 1/4	9 %6	22 ½	17 ¾	1/2	120	XSM1428	XSA1428	XSB1428	12 %	26 %	10 ¾	XHF-2	
161606	16	16	6	7 %	20 %	20 %	9 15/16	11	19 ¾	5/8	135	XSM1616	XSA1616	XSB1616	14 ¾	14 ¾	6 ¾	XHD-2	
161608	16	16	8	9 %	20 %	20 %	11 15/16	11	19 ¾	5/8	156	XSM1616	XSA1616	XSB1616	14 ¾	14 ¾	6 ¾	XHD-2	
162406	16	24	6	7 <sup>13</sup> /16	20 %	28 %	10 ¾	18 %	19 ¾	5/8	190	XSM1624	XSA1624	XSB1624	14 ½	22 ½	10 1/4	XHF-2	
162408	16	24	8	9 13/16	20 %	28 %	12 %	18 %	19 ¾	5/8	209	XSM1624	XSA1624	XSB1624	14 ½	22 ½	10 1/4	XHF-2	
162410	16	24	10	11 <sup>13</sup> / <sub>16</sub>	20 %	28 %	14 %	18 %	19 ¾	5/8	225	XSM1624	XSA1624	XSB1624	14 ½	22 ½	10 1/4	XHF-2	
162806	16	28	6	6 <sup>13</sup> /16	20 ½	32 11/16	9 ½	22 ½	19 ¾	5/8	200	XSM1628	XSA1628	XSB1628	26 ½	14 ½	12	XHF-2	
163406	16	34	6	6 15/16	20 ½	38 ½	9 ½	27	19 ¾	5/8	260	XSM1630	XSA1630	XSB1630	14 ½	28 ½	12 ½	XHF-2	
164610	16	46	10	11 <sup>13</sup> /16	20 %	50 %	14 %	39	19 ¾	5/8	390	XSM1646	XSA1646	XSB1646	14 ½	44 1/2	20 1/4	XHF-4	
181804	18	18	4	5 <sup>13</sup> ⁄16	22 %	22 %	8 ½	13	21 ¾	5/8	154	XSM1818	XSA1818	XSB1818	16 ¾	16 ¾	8 ¾	XHF-2	
181806	18	18	6	7 13/16	22 %	22 %	10 ½	13	21 ¾	5/8	177	XSM1818	XSA1818	XSB1818	16 ¾	16 ¾	8 ¾	XHF-2	
181808	18	18	8	9 13/16	22 %	22 %	12 ½	13	21 ¾	5/8	200	XSM1818	XSA1818	XSB1818	16 ¾	16 ¾	8 ¾	XHF-2	
182406	18	24	6	7 ⅓6	22 %	28 %	10 13/16	18 %	21 ¾	5/8	226	XSM1824	XSA1824	XSB1824	16 ½	22 ½	11 ½	XHF-2	
182408	18	24	8	9 1/16	22 %	28 %	12 13/16	18 %	21 ¾	5/8	239	XSM1824	XSA1824	XSB1824	16 ½	22 ½	11 ½	XHF-2	
182410	18	24	10	11 7/16	22 %	28 %	14 13/16	18 %	21 ¾	5/8	260	XSM1824	XSA1824	XSB1824	16 ½	22 ½	11 ½	XHF-2	
183008	18	30	8	9 %	22 %	34 %	12 13/16	23	21 ¾	5/8	293	XSM1830	XSA1830	XSB1830	16 ½	28 ½	14 ¾	XHF-2	
183608	18	36	8	9 %	22 %	40 %	12 %	29	21 ¾	5/8	318	XSM1836	XSA1836	XSB1836	16 ½	34 ½	18	XHF-3	
183610	18	36	10	11 %	22 %	40 %	14 %	29	21 ¾	5/8	340	XSM1836	XSA1836	XSB1836	16 ½	34 ½	18	XHF-3	
204806***	20	48	6	7 1/8	24 %	52 %	10 %	41	24	5/8	430	XSM2048	XSA2048	XSB2048	46 ½	18 ½	27	XHF-4	
242408	24	24	8	9 1/16	28 %	28 %	12 7/16	18 %	28	5/8	302	XSM2424	XSA2424	XSB2424	22	22	15 1/4	XHF-2	
242410	24	24	10	11 7/16	28 %	28 %	14 7/16	18 %	28	5/8	330	XSM2424	XSA2424	XSB2424	22	22	15 1/4	XHF-2	
243008	24	30	8	9 1/4	28 %	34 %	12 15/16	23	28	5/8	356	XSM2430	XSA2430	XSB2430	22	28	19 1/4	XHF-2	
243608	24	36	8	9 1/4	28 %	40 %	12 7/16	29	28	5/8	408	XSM2436	XSA2436	XSB2436	34	22	23 ½	XHF-3	
243610	24	36	10	11 1/4	28 %	40 %	14 %	29	28	5/8	433	XSM2436	XSA2436	XSB2436	34	22	23 ½	XHF-3	
323612*	32	36	12	12	37 ¾	41 ¾	15 ½	29	36 %	5/8	691	XSM3236	XSA3236	XSB3236	29	33	28 ¾	XHF-3	

- This unit has limited approval dependent on number of entries
- No ATEX approval
- ATEX approval but no Domestic UL & cUL approvals
  - NOTES 1. To indicate Quad-Lead bolt option, add suffix "Q" after XCE. (Not available on XCEX models.)
    - 2. Operators, windows and hinges are ordered separately.
    - 3. XCEX EEx d approval optional.
    - 4. To indicate NEMA 4/IP66 option, add suffix "N4" after size (catalog number).
    - 5. Where reference is made to Class I and Class II hazardous locations, the equipment is suitable for both Division1 and Division 2 locations.
    - 6. Enclosures are pre-drilled for mounting panel and hinge kit unless otherwise specified.




info@adalet.com

## XCE/XJF Enclosures

# XCE: Explosionproof Control Enclosures XCEX: Flameproof Control Enclosures XCEQ: Explosionproof Quad-Lead Control Enclosures

## **XJF:** Explosionproof Junction Boxes



Adalet NEMA 7/9 XCE series and XJF enclosures are used in the installation of electrical/electronic components for control, measurement or monitoring applications in hazardous environments. XCE control enclosures can be modified for installation of a variety of explosionproof operator devices, viewing windows (XJF models can not accommodate holes in cover) and accessories permitting the development of customized enclosure systems.

#### FEATURES

- Copper-free aluminum, lightweight and corrosion resistant
- Integral, cast-on mounting lugs, slotted for ease of field installation
- Drilling and tapping for left hand hinges and mounting pan (hinges and pan optional)
- Uniform wall thickness for ease of installation of control devices, windows and conduit openings
- External flange provides maximum accessibility of components mounted inside.
- Tumblast finish for quality appearance
- Premium high strength steel cover bolts, plated and coated for maximum corrosion resistance (stainless steel optional)
- Enclosures certified for field drill and tap of conduit entrances and XGC windows
- Internal grounding screw standard
- Covers exceeding approximately 75 lbs. are provided with two removable eye bolts for ease of handling
- XCE/XCEQ/XCEX certified drillable for operators at the factory or in the field
- IP66 gasket standard on XCEX
- XCEX includes IEC certification
- · XCEX includes external earthing assembly
- Quad-lead bolt (quick thread bolt) option designate XCEQ when ordering. Not available with XCEX.
- NEMA 4 (WATERTIGHT)/IP66: Features a nitrile O-Ring retained in the cover flange in a machined groove. When ordering, add N4 to the catalog number. \*Option may affect certifications consult factory.
- NEMA 6 (SUBMERSIBLE): Consult factory.

**DESIGN OPTIONS** 


- Cast-on mounting buttons, bosses and pads: Per customer specifications.
- Captive cover bolts: Consult factory, may affect approvals.
- Hinges: Left side removable standard, other locations and non-removable covers-optional.
- Windows: Circular window sizes ranging from 1" to 8" diameter viewing area. Rectangular window sizes ranging from 3" x 3" to 13" x 13" viewing
- Stainless steel cover bolts. Consult factory for NEMA 4X rating.
- Mounting Pans: Available in galvanized steel, aluminum or phenolic.
- Sidewall auxiliary device installation or machining available on XCE/XCEQ/ XCEX series enclosures Consult Factory.
- Factory machined metric sidewall threads up to M75 approved on XCE and XCEX series for Groups C & D. Group B enclosures may only have up to M30 holes

NOTE: Where reference is made to Class I and Class II hazardous locations, the equipment is suitable for both Division1 and Division2 locations.




## **CERTIFICATIONS**


### **XJF SERIES**



## **XCE/XCEQ SERIES**





### **XCEX SERIES**



NOTE: Where reference is made to Class I and Class II hazardous locations, the equipment is suitable for both Division1 and Division 2 locations.







#### **DESIGN OPTION DETAILS**

#### **MOUNTING PANS** Three Materials Available:

**Steel:** (XSM) Galvanized 12 gauge steel plate. The catalog number includes the steel mounting pan complete with 1/4" high spacers and stainless steel mounting screws.

Aluminum: (XSA) Consult factory for availability.

**Phenolic:** (XSB) A special phenolic laminated material that has high mechanical and dielectric strength. It is excellent for mounting and wiring control equipment. The catalog number includes the phenolic board, 3/8" thick, complete with 1/4" high spacers and stainless steel mounting screws.

#### NOTES 1. No installation charge when customer specifies factory installation of mounting pan.

Enclosures are pre-drilled for mounting panel unless otherwise specified.

#### **HINGE SETS**

Made of extruded aluminum alloy consisting

of two sections, female and male (with stainless steel pin) and four stainless steel hex head bolts. Designed to allow right or left hand removable or non-removable installation.

Unless specified, left hand removable hinge installation will be furnished by factory when hinged enclosures are ordered.

NOTES 1. Catalog numbers represent complete hinge sets necessary for enclosure assembly.

2. Enclosures are pre-drilled for hinge kit unless otherwise specified.

