

# Specifications



Photo is representative



## Eaton XTOE175GCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 35-175A overload range, 105 mm Frame size, NO-NC contact configuration, Selectable - 10A, 10, 20, 29 trip type

### General specifications

<b>PRODUCT NAME</b>	Eaton C440 electronic overload relay
<b>CATALOG NUMBER</b>	XTOE175GCS
<b>UPC</b>	786685533346
<b>PRODUCT LENGTH/DEPTH</b>	9 in
<b>PRODUCT HEIGHT</b>	10 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	6 lb
<b>COMPLIANCES</b>	RoHS Compliant ATEX Compliant CE Marked
<b>CERTIFICATIONS</b>	UL Listed CSA Certified EN 60947 IEC 60947

## Product specifications

OVERLOAD RANGE	35-175A
TYPE	Electronic overload relay
FRAME SIZE	105 mm
MOUNTING METHOD	Direct
CONTACT CONFIGURATION	NO, NC
TRIP TYPE	Selectable 10 A, class 10 ,20, 30

## Resources

BROCHURES	<a href="#">C440 Electronic Overload Relay</a>
CATALOGS	<a href="#">Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTOE175GCS</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

