



12-Ton C-Head Crimper, Self Contained Hydraulic, Uses U Dies, #14 AWG-750 kcmil Copper, #8 AWG-750 kcmil Aluminum, #4 AWG-556.5 kcmil ACSR

By Burndy
Catalog # [Y750HSXT](#)



12T C-Head Crimper, #14-750 kcmil CU, #8-750 kcmil AL, #4-556.5 kcmil ACSR.

Features

- Easy tool positioning with its 355 head rotation
- Patented rapid advance pump for faster crimps
- Comfort grip handles
- Audible "pop-off" pressure relief valve
- Handle drain trigger

Application

Crimping

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810458600
UPC 12 Digit	7818104586000

Dimensions

Dimensions	23.96 in x 8.71 in x 2.90 in
Height	2.90 in
Jaw Width	1.65 in
Length	23.96 in
Weight	17.2 lb
Width	8.71 in

Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Certifications and Compliance

Standards - RoHS Compliance EX Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Plastic Case

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10076340](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-Y750HSXT-SPEC-EN | REV 5/2023