ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106



YA252LN 1/0AWG Cop 2H Lug

Burndy LLC

Catalog Number	YA252LN
Manufacturer	Burndy LLC
Description	1/0 Awg Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, Ul/Csa, 90 C, Up to 35KV, Pinnk Color Code, 12 or 348 Die Index.
Weight per unit	0.1100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	12
Material	Copper
Number of Pad Holes	2
Voltage Rating	35 kV

Material, Color, and Finish

Color Code	PINK

Descriptions

Description	1/0AWG COP 2H LUG
extra long description	BUR YA252LN 1/0 CU 2-HOLE SHORT NEM
Long Description	1/0 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Pinnk Color Code, 12 or 348 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Wire Strip Length: 15/16 IN, Tongue Angle: Straight, Die Index: 12, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W25VT, W25RT, X25RT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W25VT, W25RT, X25RT Die, (2), Y35, Y39, Y750, PAT750 Tool, U25RT, U2CABT Die, (1), Y46 Tool, U25RT, U2CABT Die With PUADP-1 Adapter, (1), Co

Manufacturer Information

Brand	BURNDY
GTIN	00781810502273
Manufacturers Part Number	YA252LN
UPC	781810502273

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B