



YA25A3

by Burndy Catalog ID: YA25A3

Prop 65 Notice

Aluminum Compression Lug, 1 Hole w/o Inspection Window, 1/0 AWG, 3/8" Stud, Short Barrel, Tin Plated.

Features: Type YA-A Aluminum Tin-Plated Compression HYLUG Terminals Are Dual-Rated And Designed For Use On Both Aluminum And Copper Conductors From #12 Solid Through 2000 KCMIL, They Are Designed For Heavy Duty Applications To 35 KV, YA-A Terminals Are Prefilled With PENETROX, And Assembled With Color-Coded End Caps, Available With One, Two, And Four-Hole NEMA Tongues, The Aluminum HYLUG Terminals Are Designed For A Permanent Trouble-Free Electrical Termination, Manufactured From High Conductivity, Wrought Aluminum With Heavy Duty Wall Thickness: Provides Maximum Conductivity, Low Resistance And Ductility For An Excellent Combination Of Electrical And Crimp Forming Properties, Electro-Tin Plated: Provides Durable Long Lasting Corrosion Resistance, Internally Bevelled Barrel: Provides Easy Cable Insertion, Meets UL486B 90 DEG C Requirements: Provides A Quality Electrical Dual Connection, Connector Is Clearly Marked With Wire Size, Die Index, Color-Code And The Proper Number And Location Of Crimps: Provides Easy Identification And Tooling Recommendation For A Proper Compression Which Forms A Homogeneous Mass Resulting In An Excellent Electrical Connection, Factory Prefilled With PENETROX Oxide Inhibiting Compound: Oxide Inhibiting Compound Contains Homogeneously Suspended Metallic Particles To Penetrate The Wires Oxides, Establish Electrical Continuity And Forms An Airtight Connection, Color-Coded End Caps Inserted In Barrel End: Prevents Foreign Materials From Entering And Contaminating The Connector Prior To Usage Plus Identifies The Proper Color-Coded Die For A Reliable Connection, UL Listed 90 DEG C, 600 V - 35 KV, Finish: Electro-Tin Plated. Wire Strip Length: 1-5/16 IN, Temperature Rating: 90 DEG C, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750 Tool, U25ART Die, (1), Y46 Tool, U25ART Die With PUADP-1 Adapter, (1), Color Code: Tan, Dieless Tools (number Of Crimps): Mechanical: MY29-3, MRC840AL Tool, (1), Hydraulic HYPRESS: Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Die Index: 296

Product Details

General Application For Aluminum And Copper Conductors Color Code Tan Connector Type Terminal 296 Die Index Feature - Barrel Style Chamfered Feature - Barrel Type Standard Material Aluminum Physical Attribute - Number of Holes 1 Standard Physical Attribute - Tongue Type Plated Υ Tin - Electro Plated Plating Type Sub Brand HYLUG **Temperature Rating** 194 Trade Name HYLUG™ YA-A, Dual Rated Type

UPC	781810753101	
UPC 12 Digit	7818107531011	

Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.05 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.18 in
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.67 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.60 in
Dimension - Pad Width inch	0.82 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size inch	3/8
Dimension - Thread Size	3/8
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

BURNDY Headquarters 47 East Industrial Park Drive Manchester, New Hampshire 03109 Customer Service Hours: 8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)